

Part Number: R-3F2-L72

Voltage Indicator with 72 in Optical Cable and Zero Voltage to the Door Option

<https://shop.graceport.com/products/r-3f2-l72>







Product Specifications

Component Details	
Part Number	R-3F2-L72
Electrical Specifications	
Voltage Indicator	Flashing LEDs with "Zero' Voltage Optical Cable with 72 in cable
Voltage Type	AC/DC
Operational Voltage Range	20-600VAC 50/60Hz, 20-1000VDC
Storage Temperature Range	-45°C to + 85°C
Operational Temperature Range	-20°C to +55°C
Voltage to Door Required	No
Lead Connections	3 Phase, 4 Wire
Cable Length	72 inches
Mechanical Specifications	
Installation	30mm Pushbutton Hole
Mounting Location	External (Door/Flange Mounted)
UL Type	4X, 12, 13
Environmental Ratings	IP67, CAT III/CAT IV





Commercial Data

Country of Origin	Taiwan
Schedule B Code	8536.90.8085

Approval Certifications

Logo	Approval	Additional Text	Certificate Name	
	UL Underwriters Laboratories Inc.		E256847	
	CE European Conformity	INGR0516-A-00	SS0008-0418-A-CE	

Datasheets

Name	
Voltage Indicator Datasheet	
Voltage Indicator Datasheet Spanish	
R-3F2-LXX Datasheet	
R-3F2-LXX Installation Guide	

Don't see what you're looking for?

Contact us at sales@gracetechnologies.com, call 1-800-280-9517 or visit www.graceport.com to chat with our customer service.