

# Part Number: R-3W2MT-LMF

Multi-Environment Voltage Indicator and Safe-Test Point Combination Unit with Vertical/Flange Warning Label

<https://shop.graceport.com/products/r-3w2mt-lmf>





## Product Specifications

Component Details	
Part Number	R-3W2MT-LMF
Includes	Multi-Environment Voltage Indicator (R-3W2), Safe-Test Point (R-3MT) and Flange/Vertical Warning Label
Electrical Specifications	
Operational Voltage Range AC Single or 3-Phase	40-600 VAC; 50/60/400Hz
Operational Voltage Range DC or Stored Energy	Voltage Indicator 30 to 1000 VDC; Safe-Test Point 0 to 1000 VDC (UL Listed to 600 VDC)
Storage Temperature Range	-45°C to +85°C
Operational Temperature Range	-20°C to +55°C
Mechanical Specifications	
Installation	30mm Pushbutton Hole
UL Type	12 & 13
Orientation	Flange/Vertical
Geometric Data	
Label Width	1.90"
Label Height	10.058"





### Commercial Data

Country of Origin	Taiwan
Schedule B Code	8538.90.8160

### Approval Certifications

Logo	Approval	Additional Text	Certificate Name	
	CE European Conformity	INGR0516-A-00	SS0001-0616-A-CE	

### Datasheets

Name	
Safe-Test Point Datasheet	
Safe-Test Point Datasheet Spanish	
Voltage Indicator Datasheet	
Voltage Indicator Datasheet Spanish	

### Don't see what you're looking for?

Contact us at [sales@gracetechnologies.com](mailto:sales@gracetechnologies.com), call 1-800-280-9517 or visit [www.graceport.com](http://www.graceport.com) to chat with our customer service.