

ESG25L Battery ACSR Cutter

NEW PRODUCT

AVAILABLE AS BARE TOOL

18V Lithium-Ion



- Cuts up to 636 kcmil cable making it an excellent tool for distribution crews.
- Lightweight and very easy to handle.
- LED light provides the operator with the battery charge and tool maintenance status.
- One trigger controls all tool functions.
- Cutting head rotates 350°.
- Tools automatically retract when the cutting cycle is complete.
- Overmolded tacky grip areas make gripping the tool easier and more comfortable.

SPECIFICATIONS

| | |
|------------------------|-------------------------|
| Length | 15" (381 mm) |
| Width | 2-7/8" (73 mm) |
| Height | 4-1/2" (114 mm) |
| Weight | 4.6 lbs (2 kg) |
| Battery | 18V 3.0 Ah Li-Ion |
| Est. Cycles Per Charge | 100 |
| Capacity | Max Diameter 1" (25 mm) |
| ACSR | 636 kcmil (Grosbeak) |
| Guy Strand (not EHS) | 5/8" 16 mm |
| Ground Rod | 3/8" (9 mm) |
| Rebar (Schedule 60) | 3/8" (9 mm) |
| Wire Rope | 1/2" (13 mm) |

| CAT. NO. | UPC NO. | DESCRIPTION |
|-----------|---------|--------------------------------|
| ESG25L11 | 12383 | Cutter, ACSR BAT, 120V Charger |
| ESG25L12 | 12387 | Cutter, ACSR BAT, 12V Charger |
| ESG25L22 | 12384 | Cutter, ACSR BAT, 230V Charger |
| B ESG25LB | 01147 | ESG25 Bare Cutter |
| 76807 | 76807 | Blade Kit |

Gator® Battery-Powered Cable Cutter

AVAILABLE AS BARE TOOL

18V Lithium-Ion



- Used for cutting copper and aluminum power cables.
- State of the art 18V lithium ion (Li-ion) battery provides 70% more cycles per charge and faster cycle times.
- Retraction Stop allows the operator to stop the ram retraction at any point simply by tapping the trigger, and then starting the next cutting cycle from that point saving time and energy.
- LED light provides the operator with the battery charge and tool maintenance status.
- Two-stage hydraulic system provides fast advance and power speeds, saving time.
- Forward handle position improves tool balance.
- One trigger controls all tool functions.
- Cutting head rotates 350°
- Tools automatically retract when the cutting cycle is complete.
- Overmolded tacky grip areas make gripping the tool easier and more comfortable.
- Smart chargers maximize battery life
- U.S. Patents #6,206,663 and #6,065,326

SPECIFICATIONS BATTERY POWERED

| | |
|------------------------|------------------------------------|
| Cutting Capacity | 2" (50 mm) diameter Al or Cu cable |
| Length | 15-3/4" (400 mm) |
| Weight | 9.8 lbs. (4.4 kg) |
| Height | 13" (330 mm) |
| Battery | 18V, 3.0 Ah, Li-ion |
| Battery Charge Time | 30 minutes |
| Est. Cycles Per Charge | 300 |

| CAT. NO. | UPC NO. | DESCRIPTION |
|-----------|---------|---|
| ESG50L11 | 52129 | Battery-Powered Cable Cutter, 120 V charger |
| ESG50L12 | 52130 | Battery-Powered Cable Cutter, 12 V charger |
| ESG50L22 | 52131 | Battery-Powered Cable Cutter, 230 V charger |
| ESG50L120 | 52132 | Cable Cutter w/120V AC Adapter |
| ESG50L230 | 52133 | Cable Cutter w/230V AC Adapter |
| B ESG50LB | 01138 | ESG 50 Bare Cable Cutter |
| R 04181 | 04181 | Movable Blade |
| R 04184 | 04184 | Fixed Blade |
| R 52176 | 52176 | 18 V, 3.0 Ah, Li-ion Battery |
| R 10118 | 10118 | Carrying Case for ESG50L |
| A 12274 | 12274 | Carrying Strap |
| R 52178 | 52178 | 120V Charger |
| R 52179 | 52179 | 230V Charger |
| R 52180 | 52180 | 12V Charger |