



MC & AC CABLE & FLEXIBLE METALLIC CONDUIT FITTINGS

FLEX



TRADE SIZE	HALEX PART #	CTN/CASE QTY	CTN/CASE WT (LBS)	DIMENSIONS (IN INCHES)	
				A	B
Anti-Short Bushings				Polyethylene	
FITS CABLE RANGE: 14/2, 14/3, 12/2					
0 (5/16")	75400	10 BAGS/35 PCS	0.6	0.394	0.350
0 (5/16")	75400BP	1000	1.7	0.394	0.350
FITS CABLE RANGE: 14/4, 12/3, 6/1, 4/1					
1 (3/8")	75401	10 BAGS/35 PCS	0.45	0.450	0.410
1 (3/8")	75401BP	1000	2.0	0.450	0.410
FITS CABLE RANGE: 12/4, 10/2, 10/3, 2/1					
2 (7/16")	75402	5 BAGS/35 PCS	0.4	0.588	0.540
2 (7/16")	75402BP	500	1.2	0.588	0.540
3 (1/2")	75403	5 BAGS/20 PCS	0.3	0.780	0.730
3 (1/2")	75403BP	250	1.0	0.780	0.730
4 (3/4")	75404	4 BAGS/16 PCS	0.2	0.990	0.940
4 (3/4")	75404BP	250	1.0	0.990	0.940

APPLICATION: INDOORS ONLY - Use to protect wire within flexible metallic conduit MC and AC cable. Insert one bushing at each end of conduit or cable. **MATERIAL:** Polyethylene.
CERTIFICATIONS: TO UL AND CSA REQUIREMENTS.



TRADE SIZE	HALEX PART #	CTN/CASE QTY	CTN/CASE WT (LBS)	DIMENSIONS (IN INCHES)		
				A	A	B
				(MIN)	(MAX)	
Squeeze Connectors				Zinc Die Cast		
3/8" (1/2" ko)	04203B	50/500	3.5/35	0.58	0.61	1.00
1/2"	04205B	25/250	2.5/25	0.74	0.95	1.47
3/4"	04207B	25/250	3.3/32.5	0.88	1.11	1.58
1"	04210B	10/100	2/20	1.14	1.38	1.75
1 1/4"	04212B	10/100	2.9/29	1.42	1.65	1.91
1 1/2"	04215B	5/50	2/19.5	1.68	1.94	2.09
2"	04220B	10/40	4.6/18.4	2.08	2.56	2.34
2 1/2"	04225B	10	9	2.88	3.25	2.75
3"	04230B	5	6.5	3.34	3.63	3.19
3 1/2"	04235B	2	3	3.75	4.13	3.56
4"	04240B	1	2	4.19	4.56	3.94
WITH INSULATED THROAT						
1/2"	84205B	25/250	2.5/25	0.74	0.95	1.52
3/4"	84207B	25/250	3.3/32.5	0.88	1.11	1.63
1"	84210B	10/100	2/20	1.14	1.38	1.80
1 1/4"	84212B	10/100	2.9/29	1.42	1.65	1.96
1 1/2"	84215B	5/50	2/19.5	1.68	1.94	2.14
2"	84220B	10/40	4.6/18.4	2.08	2.56	2.39

APPLICATION: INDOORS ONLY - In a dry location, use to connect flexible metallic conduit and steel AC cable to a steel outlet box, load center or other metal enclosure. The 3/8" can also be used with steel and aluminum MC cable. **MATERIAL:** Zinc Die Cast. **MISC:** 3/8" size fits 1/2" knockout.
SUITABLE FOR: 3/8" steel flexible conduit, #14/2 wire steel armored cable, .561 steel and .538-.599 aluminum interlocked metal clad cable. 1/2" steel flexible metal conduit and #4-2 wire steel armored cable. 3/4" steel flexible metal conduit and #6-3 wire steel armored cable. 1" steel and reduced wall steel flexible metal conduit and #2-2 wire steel armored cable. 1 1/4" - 4" steel flexible metal conduit.
CERTIFICATIONS: TO UL AND CSA REQUIREMENTS.

