Aluminum Chassis (1444 & 1434 Series)



"D" & "E" Dimensions are hole center to center

KEY FEATURES

- Spot welded heavy duty construction chassis.
- Natural finish (as shown above - right group)
- Cover holes are punched with 4 holes – 3/16" diameter. Hardware not provided, please order separately - Part number **1421J6** (Pkg. of 6, 6-32 Philips head screws).

Part Number		In. Thick	Units	Dimensions				
Aluminum Chassis	Cover			A	B	C	D	E
1444-6	1434-6	.040	inch	4	4	2	3.6	3
			mm	102	102	51	92	76
1444-8	1434-8	.040	inch	6	4	2	5.6	3
			mm	152	102	51	143	76
1444-12	1434-12	.040	inch	7	5	2	6.6	3
			mm	178	127	51	168	76
1444-9	1434-10	.040	inch	8	4	1	7.6	3
			mm	203	102	25	194	76
1444-10	1434-10	.040	inch	8	4	2	7.6	3
			mm	203	102	51	194	76
1444-14	1434-14	.040	inch	9	5	2	8.6	3
			mm	229	127	51	219	76
1444-15	1434-16	.040	inch	10	6	1	9.6	4
			mm	254	152	25	244	102
1444-16	1434-16	.040	inch	10	6	2	9.6	4
			mm	254	152	51	244	102
1444-22	1434-22	.051	inch	12	8	2	11.6	6
			mm	305	203	51	295	152
1444-24	1434-22	.051	inch	12	8	3	11.6	6
			mm	305	203	76	295	152
1444-29	1434-29	.051	inch	12	10	2	11.6	8
			mm	305	254	51	295	203
1444-18	1434-18	.040	inch	13.5	5	2	13.1	3
			mm	343	127	51	333	76
1444-26	1434-26	.051	inch	16	8	2	15.6	6
			mm	406	203	51	397	152
1444-28	1434-26	.051	inch	16	8	3	15.6	6
			mm	406	203	76	397	152
1444-20	1434-20	.040	inch	17	4	3	16.6	3
			mm	432	102	76	422	76
1444-30	1434-30	.051	inch	17	10	2	16.6	8
			mm	432	254	51	422	203
1444-32	1434-30	.051	inch	17	10	3	16.6	8
			mm	432	254	76	422	203
1444-33	1434-30	.051	inch	17	10	4	16.6	8
			mm	432	254	102	422	203

CANADA
Guelph, Ontario (519) 822-2960
St. Laurent, Quebec (514) 343-9010
USA
Cheektowaga, NY (716) 651-0086

www.hammondmfg.com

EUROPE
Basingstoke, UK +44 1256 812812

AUSTRALASIA
Queenstown, SA, Australia +61 8 8240 2244

©