

Type 12 Mild Steel Two Door Wallmount Enclosure

1422 Series

Continuous Hinge Door with Handle



Application

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides a degree of protection from falling dirt, dust, oil and water.

Standards

- UL 508 Type 12
- CSA Type 12
- Complies with
 - NEMA Type 12
 - IEC 60529, IP54

Construction

- Enclosures are formed 12 or 14 gauge steel, as noted.
- Smooth, continuously welded seams without knockouts, cutouts or holes.
- Body stiffeners are provided in enclosures 30" high or more for extra rigidity.
- Welded brackets provide for enclosure mounting.
- Gasketed overlapping doors eliminate the need for a center post.
- Continuously hinged doors may be removed by pulling the hinge pin.
- Doors are secured with a three point latch and operated with a key locking automotive type handle.
- Latch rods are equipped with rollers for easier door closing.
- Oil resistant gaskets are permanently secured.
- A removable 10 gauge inner panel is included in enclosures as noted.
- Smaller sizes include a 12 gauge inner panel.
- Collar studs are provided for mounting inner panels.
- A grounding stud is provided in the enclosure and a bonding stud is provided on the door.
- A literature pocket is provided for the inside of the door.


Finish

- Cover and enclosure are phosphatized and finished in recoatable smooth ANSI 61 gray powder coating on the outside, with white powder coating on the inside.
- Removable inner panel is finished in white powder coating.


Accessories

- Inner Panels
- Blowers and Fans
- Door Stop Kit
- Cooling Products
- Ventilation
- Drip Shield Kit


- Enclosure Stabilizers
- Floor Stand Kit
- Heaters
- Type 1 Louvered Ventilating Plates
- Window Kits
- Filtered Fans
- Gland Plates
- Lighting
- Temperature Controls




Front View



Side View




Section Y-Y



Stiffener Layout
1422UX12 & 1422WW12



Section A-A
1422VX12 & 1422WW12



Section Z-Z
(Except 1422VX12 &
1422WW12)

				Body	Panel	Panel Size							Ship Wt.
Part No.	A	B	C	Gauge	Gauge	D	E	F	G	H	J	(lbs)	
1422P8	24.00	42.00	8.00	14	12	21.00	39.00	1.50	22.25	20.13	7.96	79	
1422PW8	24.00	48.00	8.00	14	12	21.00	45.00	1.50	22.25	23.13	7.96	92	
1422P10	24.00	42.00	10.00	14	12	21.00	39.00	1.50	22.25	20.13	9.96	101	
1422R10	30.00	42.00	10.00	14	12	27.00	39.00	1.50	28.25	20.13	9.96	112	
1422RW10	30.00	48.00	10.00	14	12	27.00	45.00	1.50	28.25	23.13	9.96	115	
1422RX10	30.00	60.00	10.00	14	12	27.00	57.00	1.50	28.25	29.13	9.96	142	
1422UV12	36.00	42.00	12.00	14	12	33.00	39.00	1.50	34.25	20.13	11.96	134	
1422UW12	36.00	48.00	12.00	14	12	33.00	45.00	1.50	34.25	23.13	11.96	230	
1422UX12	36.00	60.00	12.00	14	12	33.00	57.00	1.50	34.25	29.13	11.96	181	
1422VV12	42.00	42.00	12.00	14	12	39.00	39.00	1.50	40.25	20.13	11.96	152	
1422VW12	42.00	48.00	12.00	14	12	39.00	45.00	1.50	40.25	23.13	11.96	161	
1422VX12	42.13	60.06	12.69	12	10	38.00	56.00	2.00	40.25	29.13	11.96	202	
1422WW12	48.13	48.06	12.69	12	10	44.00	44.00	2.00	46.25	23.13	11.96	350	

