

Painted Diecast Aluminum Enclosures

1590 “Stomp” Series



Features

- Rugged, diecast aluminum alloy (tough - yet easy to machine), electronic instrument enclosure.
- This stock “Stomp Box” version is our popular 1590B & 1590BB & 1590XX enclosure - powder painted - to save stomp box manufacturers and experimenters time & money.
- Painted “Stomp Box” versions are coated with a smooth gloss polyester powder paint for a lasting finish, even after machining.
- Smooth paint allows for easy adhesion of labels and/or silk screens.
- Paint colors are matched to standard RAL colors (see table below).
- Lap joint construction provides protection against access of dust and splashing water. Also provides for improved EMI/RFI shielding.
- Unpainted & textured black version is also available & in many other sizes and styles - please see our 1590 series.
- Designed to meet IP54 (see gasket kit accessory below to meet IP66).
- Low side wall draft angle (2 degrees or less) for easy P.C. board mounting.
- Replacement screws - nickel plated, 6-32 x 1/2” - 1590MS100 - Package of 100. For an even funkier look - order our black replacement screws, 6-32 x 1/2” - 1590MS50BK - Package of 50

Part Number	Color	RAL Number	Units	Length	Width	Enclosure Depth (Less Lid)
1590BCB	Cobalt Blue	RAL 5013				
1590BGR	Green	RAL 6024	Inches	4.39	2.34	1.06
1590BLG	Light Gray	RAL 7035				
1590BOR	Orange	RAL 2009	mm	112	60	27
1590BRD	Red	RAL 3011				
1590BBCB	Cobalt Blue	RAL 5013				
1590BBGR	Green	RAL 6024	Inches	4.67	3.68	1.18
1590BBLG	Light Gray	RAL 7035				
1590BBOR	Orange	RAL 2009	mm	119	94	30
1590BBRD	Red	RAL 3011				
1590XXCB	Cobalt Blue	RAL 5013				
1590XXGR	Green	RAL 6024	Inches	5.72	4.77	1.39
1590XXLG	Light Gray	RAL 7035				
1590XXOR	Orange	RAL 2009	mm	145	121	35
1590XXRD	Red	RAL 3011				