

Metering Cabinets NEMA 1



Application

- Designed for indoor housing of metering transformers.

Standards

- CSA Approved

Construction

- Formed and spot welded from 14 or 16 gauge steel.
- Spot welded construction and formed edges.
- Removable inner panel.
- Hinged covers.
- 2 cutouts in top of each cabinet with metering plates included.

Finish

- Enclosure and cover are finished in ANSI/ASA 61 gray inside and out.

Part No.	Dimensions			Panel Dimensions	Type of Door	Latch Type	Latch Qty	Metering Plates	Ship Wt. lbs.
	A	B	C						
CMC202010	20	20	10	16 x 16	Single	Hasp	2	2	42
CMC271310*	27	13	10	23 x 9	Single	Hasp	2	0	38
CMC302010	30	20	10	26 x 16	Single	Hasp	2	2	69
CMC303010	30	30	10	26 x 26	Double	2 Hasp + Quarter Turn	3	2	92
CMC363612	36	36	12	32 x 32	Double	2 Hasp + Quarter Turn	3	2	131
CMC484812	48	48	12	44 x 44	Double	2 Hasp + Quarter Turn	3	2	210

* no cutouts in top or metering plates