

Type 4X Stainless Steel Wallmount Enclosure *Waterfall Series*



Application

- Designed to enclose electrical and/or electronic equipment and protect against harsh, industrial environments for wallmount applications.
- Sloped top prevents water from resting on top as well as providing potential for controls mounting.
- Unique hinge design allows for easy cleaning in hose-down environments.
- A wide range of sizes and practical accessories make this product line a complete package.

Standards

- UL 508 Type 3R, 4, 4X and 12
- CSA Type 3R, 4, 4X and 12
- NSF - ANSI 169
- Complies with
 - NEMA 3R, 4, 4X, 12 and 13
 - IEC 60529, IP 66

Construction

- Formed 304 or 316L stainless steel.
- Continuously welded seams ground smooth.
- Door stiffeners are provided where required for increased strength and rigidity - designed to also permit additional mounting options.
- Formed lip on enclosure to exclude flowing liquids and contaminants.
- Door latches (316 stainless steel quarter turns) feature the added safety of quarter turn slot requiring use of tool for opening.
- Door hinges (316 stainless steel) are easy to clean, provide 180 degree opening, are easily removed for modifications and are interchangeable.
- Seamless poured-in place gasket.
- Collar studs provided for mounting inner panel.
- Includes hardware kit with panel mounting nuts and sealing washers for wall mounting holes.
- Bonding stud provided on door and grounding stud installed in enclosure.


Finish

- Cover and enclosure are natural stainless steel with a smooth brushed finish.

Accessories

- Cooling Products
- Ventilation
- Filtered Fans
- Blowers and Fans
- Door Stop Kit
- Heaters

- Handles
- Washdown Quarter Turn Assemblies
- Mounting Foot Kit
- Padlock Adaptor
- Quarter Turn Assemblies
- Type 4 Hardware Kits
- Gland Plates
- Floor Stand Kit
- Inner Panels
- Quarter Turn Inserts and Keys
- Wallmount Stand-offs
- Rear Hole Plugs
- Temperature Controls
- Mild Steel and Stainless Steel Window Kits
- Deep Hinged Window Kits
- Wash Down Floor Stand Kit



304 S.S. Part No.	316 S.S. Part No.	Overall Dimensions					Opt. Panel Part No.	Galv. Steel Part No.	Latch Qty	Hinge Qty
		A1	A2	B	C	G				
HWST16128SS	HWST16128S16	16.00	19.70	12.00	8.00	14.50	18P1309	18G1309	2	2
HWST16168SS	HWST16168S16	16.00	19.70	16.00	8.00	14.50	18P1313	18G1313	2	2
HWST20168SS	HWST20168S16	20.00	23.70	16.00	8.00	18.50	18P1713	18G1713	2	2
HWST20208SS	HWST20208S16	20.00	23.70	20.00	8.00	18.50	18P1717	18G1717	2	2
HWST24208SS	HWST24208S16	24.00	27.70	20.00	8.00	22.50	18P2117	18G2117	2	2
HWST24248SS	HWST24248S16	24.00	27.70	24.00	8.00	22.50	18P2121	18G2121	4	2
HWST30248SS	HWST30248S16	30.00	33.70	24.00	8.00	28.50	18P2721	18G2721	4	3
HWST30308SS	HWST30308S16	30.00	33.70	30.00	8.00	28.50	18P2727	18G2727	4	3
HWST36308SS	HWST36308S16	36.00	39.70	30.00	8.00	34.50	18P3327	18G3327	5	3
HWST201612SS	HWST201612S16	20.00	25.50	16.00	12.00	18.50	18P1713	18G1713	2	2
HWST202012SS	HWST202012S16	20.00	25.50	20.00	12.00	18.50	18P1717	18G1717	2	2
HWST242412SS	HWST242412S16	24.00	29.50	24.00	12.00	22.50	18P2121	18G2121	4	2
HWST302412SS	HWST302412S16	30.00	35.50	24.00	12.00	28.50	18P2721	18G2721	4	3
HWST363012SS	HWST363012S16	36.00	41.50	30.00	12.00	34.50	18P3327	18G3327	5	3
HWST363612SS	HWST363612S16	36.00	41.50	36.00	12.00	34.50	18P3333	18G3333	5	3
HWST363016SS	HWST363016S16	36.00	43.40	30.00	16.00	34.50	18P3327	18G3327	5	3

304 S.S. Part No.	316 S.S. Part No.	Overall Dimensions					Opt. Panel	Galv. Steel	Latch	Hinge
		A1	A2	B	C	G	Part No.	Part No.	Qty	Qty
HWST483616SS	HWST483616S16	48.00	55.40	36.00	16.00	46.50	18P4533	18G4533	5	4
HWST603616SS	HWST603616S16	60.00	67.40	36.00	16.00	58.50	18P5733	18G5733	5	4

Data subject to change without notice

© 2015. Hammond Manufacturing Ltd. All rights reserved.