

Formed Steel Rack Panels *PBFS Series*

Features

- Constructed of 16-gauge steel.
- Fits standard EIA-310-D compliant rails.
- Install in unused rack space to improve both cooling efficiency and prevent air re-circulation.
- Finished in smooth powder paint.
- RoHS Compliant.
- Manufactured in North America.



Accessories

- Mounting Hardware



Part No. Black	Part No. ASA 61 Gray	Part No. Light Gray	Panel Height		Number of Mounting Slots
			Units	Rack Units	
PBFS19000BK2	-	-	0.0875	1/2U	2
PBFS19001BK2	PBFS19001GY2	PBFS19001LG2	1.75	1U	4
PBFS19003BK2	PBFS19003GY2	PBFS19003LG2	3.50	2U	4
PBFS19005BK2	PBFS19005GY2	PBFS19005LG2	5.25	3U	4
PBFS19007BK2	PBFS19007GY2	PBFS19007LG2	7.00	4U	4
PBFS19008BK2	PBFS19008GY2	PBFS19008LG2	8.75	5U	4
PBFS19010BK2	PBFS19010GY2	PBFS19010LG2	10.50	6U	8
PBFS19012BK2	PBFS19012GY2	PBFS19012LG2	12.25	7U	8
PBFS19014BK2	PBFS19014GY2	PBFS19014LG2	14.00	8U	8
PBFS19015BK2	PBFS19015GY2	PBFS19015LG2	15.75	9U	8
PBFS19017BK2	PBFS19017GY2	PBFS19017LG2	17.50	10U	8
PBFS19019BK2	PBFS19019GY2	PBFS19019LG2	19.25	11U	8
PBFS19021BK2	PBFS19021GY2	-	21.00	12U	8
PBFS19022BK2	PBFS19022GY2	PBFS19022LG2	22.75	13U	8
PBFS19024BK2	PBFS19024GY2	-	24.50	14U	10
PBFS19026BK2	PBFS19026GY2	-	26.25	15U	10
PBFS19028BK2	PBFS19028GY2	-	28.00	16U	12
PBFS19029BK2	PBFS19029GY2	-	29.75	17U	12
PBFS19031BK2	PBFS19031GY2	-	31.50	18U	12

Data subject to change without notice