


## Short on time? Click here to see our Pre-Assembled C4RR Cabinet Series

### Gallery



### Accessories

Cabinet Fan Tops  
 Contempra Cabinet Door  
 Replacement Lock  
 Universal Rack Shelf

Adjustable Depth 4-Post Rack  
 Mount Shelf  
 Four Post Mounting Sliding Shelf  
 Sliding Keyboard Shelf  
 Horizontal Lacing Strip  
 Horizontal Steel Finger Cable  
 Manager  
 Horizontal Hinged Cable Guide  
 Outlet Strips  
 Grounding  
 Caster Set

Side Panel Locking Kit  
 Rack and Cabinet  
 Baying/Ganging/Joining Kit  
 Vertical Cabinet Cable Manager  
 with Door  
 Rack Mount Locking Storage  
 Drawer  
 Rack Unit Label  
 Adjustable Depth Cable Manager  
 Horizontal Ring Cable Manager  
 Horizontal Hinged Cable Manager  
 Vertical Cable Tray  
 Rack Panels  
 Mounting Hardware

### C4 Open Frames and Rail Options

Part No.	Overall Dimensions			Usable Mounting Dimensions		Rack Units	Mounting Rail Options	
	Height	Width	Depth	Height	Depth		Tapped 10-32	Square Hole
C4F244231BK1	48.50	24.00	31.50	42.00	29.50	24U	Not Available	C4PR2442SZPL
C4F244236BK1	48.50	24.00	36.00	42.00	34.00	24U	Not Available	C4PR2442SZPL
C4F244242BK1	48.50	24.00	42.00	42.00	40.00	24U	Not Available	C4PR2442SZPL
C4F247331BK1	79.30	24.00	31.50	73.00	29.50	42U	C4PR2473TZPL	C4PR2473SZPL
C4F247336BK1	79.30	24.00	36.00	73.00	34.00	42U	C4PR2473TZPL	C4PR2473SZPL
C4F247342BK1	79.30	24.00	42.00	73.00	40.00	42U	C4PR2473TZPL	C4PR2473SZPL
C4F247731BK1	83.50	24.00	31.50	77.00	29.50	44U	C4PR2477TZPL	C4PR2477SZPL
C4F247736BK1	83.50	24.00	36.00	77.00	34.00	44U	C4PR2477TZPL	C4PR2477SZPL
C4F247742BK1	83.50	24.00	42.00	77.00	40.00	44U	C4PR2477TZPL	C4PR2477SZPL
C4F307731BK1	83.50	30.00	31.50	77.00	29.50	44U	C4PR77TZPL	C4PR77SZPL
C4F307736BK1	83.50	30.00	36.00	77.00	34.00	44U	C4PR77TZPL	C4PR77SZPL
C4F307742BK1	83.50	30.00	42.00	77.00	40.00	44U	C4PR77TZPL	C4PR77SZPL

### C4 Doors

Part No. Solid Door	Part No. Acrylic Door	Part No. Perforated	Part No. Perforated Split Doors	Use with Cabinet	
				Rack Units	Width
C4DF2442SBK1	C4DF2442PBK1	C4DF2442VBK1	C4BD2442VBK1	24U	24.00
C4DF2473SBK1	C4DF2473PBK1	C4DF2473VBK1	C4BD2473VBK1	42U	24.00
C4DF2477SBK1	C4DF2477PBK1	C4DF2477VBK1	C4BD2477VBK1	44U	24.00
C4DF3077SBK1	C4DF3077PBK1	C4DF3077VBK1	C4BD3077VBK1	44U	30.00

\*Perforated doors for both front and back of the cabinet are suggested for most server applications.

## C4 Side Panels (Sold in Pairs)

Part No. Solid	Part No. Vented	Use with Cabinet	
		Rack Units	Depth
C4SP4231SBK1	C4SP4231VBK1	24U	31.50
C4SP4236SBK1	C4SP4236VBK1	24U	36.00
C4SP4242SBK1	C4SP4242VBK1	24U	42.00
C4SP7331SBK1	C4SP7331VBK1	42U	31.50
C4SP7336SBK1	C4SP7336VBK1	42U	36.00
C4SP7342SBK1	C4SP7342VBK1	42U	42.00
C4SP7731SBK1	C4SP7731VBK1	44U	31.50
C4SP7736SBK1	C4SP7736VBK1	44U	36.00
C4SP7742SBK1	C4SP7742VBK1	44U	42.00
C4SP7731SBK1	C4SP7731VBK1	44U	31.50
C4SP7736SBK1	C4SP7736VBK1	44U	36.00
C4SP7742SBK1	C4SP7742VBK1	44U	42.00

## C4 Top Panels

Part No. Solid Top Panel	Part No. Vented Top Panel	Part No. Fan Cutouts Top Panel	Part No.	Part No.	Use with Cabinet	
			Four (4) 4.7" 100CFM Fans With Thermostat Top Panel	One (1) 10" 550 CFM Fan Without Thermostat Top Panel	Width	Depth
C2T1923SBK1	C2T1923VBK1	C2T1923FBK1	C2T1923F4TBK1	C2T1923F10BK1	24.00	31.50
C2T1931SBK1	C2T1931VBK1	C2T1931FBK1	C2T1931F4TBK1	C2T1931F10BK1	24.00	36.00
C2T1936SBK1	C2T1936VBK1	C2T1936FBK1	C2T1936F4TBK1	C2T1936F10BK1	24.00	42.00
C2T2423SBK1	C2T2423VBK1	C2T2423FBK1	C2T2423F4TBK1	C2T2423F10BK1	30.00	31.50
C2T2431SBK1	C2T2431VBK1	C2T2431FBK1	C2T2431F4TBK1	C2T2431F10BK1	30.00	36.00
C2T2436SBK1	C2T2436VBK1	C2T2436FBK1	C2T2436F4TBK1	C2T2436F10BK1	30.00	42.00

## C4 Bottom Panel

Part No.	Use with Cabinet	
	Width	Depth
C4B2431SBK1	24.00	31.50
C4B2436SBK1	24.00	36.00
C4B2442SBK1	24.00	42.00
C4B3031SBK1	30.00	31.50
C4B3036SBK1	30.00	36.00
C4B3042SBK1	30.00	42.00

## C4 Vertical Cable Manager

Part No.	Description	Use with Cabinet
		Rack Units
VCT42	Cable Tray	24U

Part No.	Description	Use with Cabinet
		Rack Units
VCT73	Cable Tray	42U
VCT77	Cable Tray	44U
VCTPDU73	Cable Tray with Tooless PDU Bracket	42U
VCTPDU77	Cable Tray with Tooless PDU Bracket	44U
C4VCM42BK1	Cable Manager w/Door	24U
C4VCM73BK1	Cable Manager w/Door	42U
C4VCM77BK1	Cable Manager w/Door	44U

## C4 Right-Hand Hinge

Part No.	C4RHINGE
----------	----------

*Data subject to change without notice*

© 2014. Hammond Manufacturing Ltd. All rights reserved.