

Heavy Duty Adjustable Depth Pivoting Wall Mount Rack *HWMR Series*



The Hammond Wall Mount Rack (HWMR) series was designed to easily mount network equipment in IT environments with limited floor space. Unlike similar racks, Hammond has integrated both depth adjustment and pivoting swing out capabilities in one rugged open rack system. Available in 12U, 20U, 24U and 32U rack unit options the HWMR can easily adjust in depth from eighteen to twenty-four inches to accommodate a wide range of equipment sizes.

Features

- Constructed of heavy duty 12 gauge steel (braces and rack rail); 16 gauge steel (other body components).
- EIA compliant square-hole rails with rail unit space markers.
- Rack frame pivots on center providing convenient equipment access without exceeding the rack footprint.
- Adjustable variable depth from 18" to 24" using slots for easy set-up and adjusting.
- Three (3) spring pin positions allow for simplified equipment maintenance.
- Side and rear cable access with multiple tie points for cable management.
- Finished in smooth black powder paint.
- Knockdown design ships unassembled for easy handling and shipping protection.
- Tested to nearly double the suggested load rating of 220 lbs.
- RoHS Compliant.
- Manufactured in North America.

Included in the Box

- HWMR Components and assembly hardware.
- Assembly Bulletin.
- Wall mounting template for easy 16 inch center installation. (Wall mounting hardware not included)
- Fifty (50) pack of 10-32 screws and cage nuts.

Video

Accessories

Universal Rack Shelf
Two Post Mounting Clamping Shelf
Adjustable Depth DIN Rail Panel
Outlet Strips
Cable Management
Mounting Hardware

Two Post Mounting Adjustable Shelf
Two Post Mounting Keyboard & Equipment Shelf
Hinged Acrylic Door Panel Cover
Rack Panels
Rail Mounting Cable Ring
Rack Unit Label

Part No.	Overall Dimensions		Mounting (Usable) Dimensions				Rack Units	Shipping Weight
	Height	Width	Height	Width	Min Depth	Max Depth		
HWMR1912UBK	26.50	20.00	21.00	19.00	18.00	24.00	12U	38
HWMR1920UBK	40.50	20.00	35.00	19.00	18.00	24.00	20U	43
HWMR1924UBK	47.50	20.00	42.00	19.00	18.00	24.00	24U	45
HWMR1932UBK	61.50	20.00	56.00	19.00	18.00	24.00	32U	50

Includes a fifty (50) pack of 10-32 screws and cage nuts.

Data subject to change without notice