



Quality Products. Service Excellence.

## Soft Grip Cabinet Caster Set *1425BLSOFT Series*

660 lbs (299 kg) Weight Capacity



### Features

- Unique soft tread design ideal for medical, office and institutional environments.
- Twin wheels increase ease of swivel for added maneuverability.
- Quiet and non-marketing thermoplastic elastomer wheel treads provide floor protection.
- All casters include peddle lock.
- Includes mounting hardware.
- Grey finish with plated zinc top plate and stem.
- RoHS and REACH Compliant.

### Compatibility

- C2/C2RR | Equipment Cabinet
- C4/C4RR | Server Cabinet
- DNRRLDK | 2-Post Open Frame Rack
- SDC | Low-Profile Server Cabinet
- RCK | Knockdown Equipment Cabinet
- RCSC | Knockdown Server Cabinet



Part No.	Strength	Wheel Diameter	Overall Height		Hole Mounting Pattern		Caster Set Weight Capacity	Qty Included In Set	Brakes Included
			Added to Cabinet		Width	Depth			
1425BLSOFT	Light Duty	2.95	3.50		1.75	3.00	660 lbs (299 kg)	4	Yes

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.