



Quality Products. Service Excellence.

## Deep Hinged HMI Cover Kits *1481SDH Series*



### Features

- Extra deep kits are designed to provide protection and easy access to components and equipment installed inside an enclosure.
- Frame is 14 gauge mild steel or 316L stainless steel.
- Maintain environmental protection level of enclosure. Painted mild steel maintain Type 4 and 12. Stainless Steel maintain Type 4, 4X and 12.
- Quarter turn latch for easy access.
- 2.5 inches of extra usable depth
- Oil resistant neoprene gasket ensures a watertight seal.
- Hinges can be oriented in any direction.
- Conveniently sized to allow mounting on any enclosure with a suitable mounting surface.
- Mounting hardware and template are included.
- Finished in ANSI 61 gray recoatable powder or natural brushed stainless steel.



Painted Steel Part No.	316 Stainless Steel Part No.	Overall Dimensions		Latch Qty	Maximum Cut-Out Size	
		H	W			
1481SDH1418	1481SSDH1418	12.19	14.56	1.00	9.19	11.56
1481SDH1612	1481SSDH1612	14.19	8.14	1.00	11.19	5.14
1481SDH1620	1481SSDH1620	14.19	16.14	1.00	11.19	13.14
1481SDH1624	1481SSDH1624	14.19	20.14	1.00	11.19	17.14
1481SDH2016	1481SSDH2016	18.19	12.14	1.00	15.19	9.14
1481SDH2024	1481SSDH2024	18.19	20.14	1.00	15.19	17.14
1481SDH2416	1481SSDH2416	22.19	12.14	1.00	19.19	9.14
1481SDH2420	1481SSDH2420	22.19	16.14	1.00	19.19	13.14
1481SDH2430	1481SSDH2430	22.19	26.14	1.00	19.19	23.14
1481SDH3024	1481SSDH3024	28.19	20.14	2.00	25.19	17.14
1481SDH3624	1481SSDH3624	34.19	20.14	2.00	31.19	17.14

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.