



Quality Products. Service Excellence.

## Rack Mount Basic PDU 1582 Series

15A | Single-Phase 125V | Front Facing 5-15R Outlets

### Features

- Designed for power distribution from the front of the unit.
- 1U horizontal 19" rackmount installation.
- Available with lighted on/off switch or red pilot light to indicate power on.
- Available in ASA 61 grey or black powder coat finish.
- [Click here for our surge protected version.](#)



### Specifications

- Heavy duty 14 gauge wire cord - 14/3 SJT type for extreme temperature ranges and integral molded plug.
- Plug types available are NEMA 5-15P straight blade or NEMA L5-15P locking type.
- Includes 15 Amp, 125 VAC circuit breaker to prevent accidental overload.
- 6 outlet models include 2 outlets with extra spacing for clearance of most plug in transformers.
- UL/cUL recognized Standard UL1363 file No. E166039 & CSA C22.2 No. 308-14 & CSA C22.2 No. 0.4-04



### Gallery



### Accessories

- Mounting Hardware
- Rail Depth Adapter Kit

### Black Finish

Illuminated On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions			Number of Outlets		NEMA Type		Plug			Cord Length	Rack Units
		Height	Width	Depth	Front	Rear	Outlet	Plug	Blade Type	Rotated Outlets			
1582H6A1BK	1582T6A1BK	1.72	19.00	2.66	6	0	5-15R	5-15P	Straight	No	6 ft	1U	
1582H6A1BKRA	1582T6A1BKRA	1.72	19.00	2.66	6	0	5-15R	5-15P	Straight	Yes	6 ft	1U	
1582H6B1BK	1582T6B1BK	1.72	19.00	2.66	6	0	5-15R	5-15P	Straight	No	15 ft	1U	
1582H6B1BKRA	1582T6B1BKRA	1.72	19.00	2.66	6	0	5-15R	5-15P	Straight	Yes	15 ft	1U	
1582H6C1BK	1582T6C1BK	1.72	19.00	2.66	6	0	5-15R	L5-15P	Locking	No	6 ft	1U	
1582H6C1BKRA	1582T6C1BKRA	1.72	19.00	2.66	6	0	5-15R	L5-15P	Locking	Yes	6 ft	1U	
1582H6D1BK	1582T6D1BK	1.72	19.00	2.66	6	0	5-15R	L5-15P	Locking	No	15 ft	1U	
1582H6D1BKRA	1582T6D1BKRA	1.72	19.00	2.66	6	0	5-15R	L5-15P	Locking	Yes	15 ft	1U	
1582H8A1BK	1582T8A1BK	1.72	19.00	2.66	8	0	5-15R	5-15P	Straight	No	6 ft	1U	
1582H8B1BK	1582T8B1BK	1.72	19.00	2.66	8	0	5-15R	5-15P	Straight	No	15 ft	1U	
1582H8C1BK	1582T8C1BK	1.72	19.00	2.66	8	0	5-15R	L5-15P	Locking	No	6 ft	1U	
1582H8D1BK	1582T8D1BK	1.72	19.00	2.66	8	0	5-15R	L5-15P	Locking	No	15 ft	1U	

**ASA 61 Grey Finish**

Illuminated On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions			Number of Outlets		NEMA Type		Plug		Rotated Outlets	Cord Length	Rack Units
		Height	Width	Depth	Front	Rear	Outlet	Plug	Blade Type				
1582H6A1	1582T6A1	1.72	19.00	2.66	6	0	5-15R	5-15P	Straight	No	6 ft	1U	
1582H6B1	1582T6B1	1.72	19.00	2.66	6	0	5-15R	5-15P	Straight	No	15 ft	1U	
1582H6C1	1582T6C1	1.72	19.00	2.66	6	0	5-15R	L5-15P	Locking	No	6 ft	1U	
1582H6D1	1582T6D1	1.72	19.00	2.66	6	0	5-15R	L5-15P	Locking	No	15 ft	1U	
1582H8A1	1582T8A1	1.72	19.00	2.66	8	0	5-15R	5-15P	Straight	No	6 ft	1U	
1582H8B1	1582T8B1	1.72	19.00	2.66	8	0	5-15R	5-15P	Straight	No	15 ft	1U	
1582H8C1	1582T8C1	1.72	19.00	2.66	8	0	5-15R	L5-15P	Locking	No	6 ft	1U	
1582H8D1	1582T8D1	1.72	19.00	2.66	8	0	5-15R	L5-15P	Locking	No	15 ft	1U	

*Data subject to change without notice*

© 2021. Hammond Manufacturing Ltd. All rights reserved.