


Class 2 Energy Limiting Box Mount *BF Series*



Features

- Used in chimes, door bells, security systems, decorative lighting, furnaces, humidifiers, appliances, vending machines, intercom system type applications.
- Rugged, low noise design, indoor use only.
- Stripped wire input (primary) leads, screw terminal output (secondary).
- Mounted on box plate for easy installation.
- Input leads are black 6" minimum, on 240V models 240V lead is red.
- All models are designed for 50/60 Hz. operation - limited by built in circuit breaker.
- c UL us listed #E184371 - Class 2 Not inherently limited
- CSA certified (209651)



Part No.	A.C. Input (Primary) V (RMS)	A.C. Output Secondary (RMS)		Power Rating VA	Overall Dimensions		
		V	A		A	B	C
BF2F	120	16	4.68	75	3.00	2.50	3.75
BF5F	240	16	4.68	75	3.00	2.50	3.75
BF2G	120	24	3.13	75	3.00	2.50	3.75
BF5G	240	24	3.13	75	3.00	2.50	3.75



Data subject to change without notice