



Quality Products. Service Excellence.

Gland Plates *GPM Series*

Features




- 14 gauge steel gland plate allows for easy cable entry into enclosure
- Maintains NEMA 12, 4 rating, Stainless plates hold type 4X rating
- Hardware and cutout template included
- Modified sizes are available:
 - 16 gauge mild or stainless 76" x 18"
 - 14 gauge mild or stainless 76" x 25"
 - 12 and 10 gauge mild or stainless 76" x 40"
 - 0.081 aluminum 76" x 18"
 - 0.100 aluminum 76" x 25"

Finish

- Available in ANSI 61 Gray and RAL 7035 Light Gray
- Stainless Plates are 316 with a number 4 brush finish

Gallery



Part No.	Finish	Overall Dimensions		Fits Opening	
		H	W	H	W
GP1507LG	RAL 7035 Light Gray	15.00	7.50	12.00	4.50
GP2207LG	RAL 7035 Light Gray	22.00	7.50	19.00	4.50
GP1507GY	ANSI 61 Gray	15.00	7.50	12.00	4.50
GP2207GY	ANSI 61 Gray	22.00	7.50	19.00	4.50
GP1507S16	316 STAINLESS	15.00	7.50	12.00	4.50
GP2207S16	316 STAINLESS	22.00	7.50	19.00	4.50

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.