



Quality Products. Service Excellence.

Low-Profile Wall Mount Rack Cabinet *HLP Series*

UL Rated 200 lbs (90 kg) Weight Capacity



The HLP is a perfect solution for your networking and server installations when space is tight.

Features

- Available in two (2) heights up to 41 inches of usable space, and three (3) fixed rack unit options.
- Each cabinet ships with one (1) pair of 2U 180-degree rotating mounting rack rails and one (1) pair of fixed rack rails.
 - Fixed rack mounting units available in 4U, 6U and 8U.
 - Fixed rails mount at five different angles, providing equipment mounting options.
 - Includes starter pack of **SCREW1032-25** screws.
- Locking hinged front door includes side venting for airflow.
 - Door and latch can be reversed to swing left-to-right.
- Rear wall mounting section features 3.00", 2.00", 1.38" and 1.12" conduit knockouts on top and bottom.
- Side venting is designed for optional fans for active cooling.
- Generous cable management lances located on the rear section.
- Heavy duty keyhole for wall mounting.
- Large knockouts in rear for cable access.

Specifications

- Body and rear section constructed of 16-gauge steel.
- Rack rails are 14-gauge steel with 10-32 tapped EIA compliant mounting rails.
- Body includes dedicated bonding points which also provides the option of drill-less mounting of electrical 4x2 utility boxes.
 - Grounding kit sold separately - **GRDKIT01** or **GRDKIT04**.
- UL Listed 2416 load rated for up to 200 lbs (90 kg). Static Load tested to 800 lbs (362 kg)
- Body and door are finished in rugged sand-textured black or textured RAL 7035 light gray powder paint. The rack rails are finished in smooth white powder paint.
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.



Upgrade the cabinet to be dust-resistant with the **HWCF** Cabinet Sealing and Filter Kit.

Accessories

- Universal Rack Shelf
- Hook and Loop Roll
- Bonding Wire Kits
- Two Post Mounting Clamping Shelf
- Fan Kits
- 10-32 Mounting Screw and Clip Nut Combo-Pack
- PDUs and Outlet Strips



Part No. Black	Part No. Light Gray	Overall Dimensions			Rack Units	Maximum Vertical Usable Depth	
		Height	Width	Depth		Both Rails Installed	Fixed Rail Only
HLP4U31BK	HLP4U31LG	31.00	27.50	11.15	2U + 4U	21.90	26.90
HLP4U43BK	HLP4U43LG	43.00	27.50	11.15	2U + 4U	33.90	38.90
HLP6U31BK	HLP6U31LG	31.00	27.50	15.46	2U + 6U	21.90	26.90
HLP6U43BK	HLP6U43LG	43.00	27.50	15.46	2U + 6U	33.90	38.90
HLP8U31BK	HLP8U31LG	31.00	27.50	19.65	2U + 8U	21.90	26.90
HLP8U43BK	HLP8U43LG	43.00	27.50	19.65	2U + 8U	33.90	38.90

Optional 180-Degree Rotating Mounting Rail Kits

Part No.	Mounting Dimensions		Rack Units	Rotation	EIA Rail Type	Paint Finish
	Height	Width				
HLP2UR	3.50	19.00	2U	180 Degrees	10-32 Threaded	Smooth White
HLP4UR	7.00	19.00	4U	180 Degrees	Clip Nut Round Hole	Smooth Black
HLP6UR	10.50	19.00	6U	180 Degrees	Clip Nut Round Hole	Smooth Black
HLP8UR	14.00	19.00	8U	180 Degrees	Clip Nut Round Hole	Smooth Black

Tags: **Remote Premise Box***Data subject to change without notice*

