



*Quality Products. Service Excellence.*

## Hole Plugs *HP Series*



### Features

- Designed to seal unused pushbutton holes, conduit openings and knockout holes against dust, oil and water.
- Standard Pushbutton size is 30.5mm; Mini Pushbutton size is 22.5mm
- **Steel Hole Plug**
  - Available in 12 sizes.
  - Finished in 2 color options - ANSI 61 gray or RAL7035 Light Gray
  - Oil resistant gasket.
  - Secured with an 10-24 x 0.55" threaded stud and plated wing nut.
- **Stainless Steel Hole Plugs**
  - Available in 8 sizes.
  - Finished in brushed natural 304 stainless steel finish.
  - Oil resistant gasket.
  - Secured with an 10-24 x 0.55" threaded stud and plated wing nut.

### Steel

| ANSI 61<br>Gray | RAL7035 Lt<br>Gray |                      |                      |                  |
|-----------------|--------------------|----------------------|----------------------|------------------|
| Part No.        | Part No.           | Description          | Max Hole<br>Diameter | Plug<br>Diameter |
| HP22            | HP22LG             | 22mm Mini Pushbutton | 0.88                 | 1.22             |
| HP50            | HP50LG             | .5" Conduit          | 0.88                 | 1.38             |
| HP75            | HP75LG             | .75" Conduit         | 1.06                 | 1.56             |
| HPB             | HPBLG              | Std. Pushbutton      | 1.25                 | 1.75             |
| HP100           | HP100LG            | 1" Conduit           | 1.38                 | 1.88             |
| HP125           | HP125LG            | 1.25" Conduit        | 1.69                 | 2.19             |
| HP150           | HP150LG            | 1.5" Conduit         | 2.00                 | 2.50             |
| HP200           | HP200LG            | 2" Conduit           | 2.50                 | 3.00             |
| HP250           | HP250LG            | 2.5" Conduit         | 3.00                 | 3.50             |
| HP300           | HP300LG            | 3" Conduit           | 3.62                 | 4.12             |
| HP350           | HP350LG            | 3.5" Conduit         | 4.12                 | 4.62             |
| HP400           | HP400LG            | 4" Conduit           | 4.62                 | 5.12             |

### Stainless Steel

| Part No. | Description     | Max Hole Diameter | Plug Diameter |
|----------|-----------------|-------------------|---------------|
| HP22SS   | 22mm Pushbutton | 0.88              | 1.22          |
| HP50SS   | .5" Conduit     | 0.88              | 1.38          |
| HP75SS   | .75" Conduit    | 1.06              | 1.56          |
| HPBSS    | Std. Pushbutton | 1.25              | 1.75          |
| HP100SS  | 1" Conduit      | 1.38              | 1.88          |
| HP125SS  | 1.25" Conduit   | 1.69              | 2.19          |
| HP150SS  | 1.5" Conduit    | 2.00              | 2.50          |
| HP200SS  | 2" Conduit      | 2.50              | 3.00          |

© 2021. Hammond Manufacturing Ltd. All rights reserved.