



Quality Products. Service Excellence.

Swing-Out Sectional Floor/ Wall Mount Rack Cabinet *HWF Series*

500 lbs (226 kg) Weight Capacity



Features

- Available in three (3) heights
- Optional doors install in minutes and are available in vented, tinted window and solid.
- Top of rear section includes a 3U cutout for optional rack mount fans or accessory mounting.
- Main body can be installed to swing from left-to-right or right-to-left. Includes locking twist-latches.
- Includes one (1) pair of adjustable depth threaded 10-32 EIA compliant mounting rack rails.
 - Thirty (30) inch wide mounting rails include cutouts for optional 1U 19" accessories, such as cable management or power bars.
 - 10-32 tapped rails are easy to remove on-site and replace with square hole rails (sold separately) if needed.
- Includes starter pack of **SCREW1032-50** screws and **CLPKIT1032-25** clip nuts and screws.

Specifications

- Heavy duty rear and base are constructed in 14-gauge welded steel.
- Optional locking doors are constructed in 16-gauge steel.
- Swing-out cabinet constructed in 16-gauge welded steel and features a spring-hinge pin for easy installation and removal.
- 2.50" and 2.00" conduit knockouts are located on the side.
- 4.00", 2.00" conduit knockouts and BNC 0.625" knockouts are located on the top.
- Numerous cable management mounting points included.
- Heavy duty keyhole for wall mounting and leveling feet.
- Large openings in rear for cable access designed for mounting over electrical receptacles.
- Dedicated bonding and grounding points that also provide drill-less mounting of electrical utility boxes. **Ground Cable Kit** sold separately.
- Load rated for up to 500 lbs (226 kg).
- Rugged textured black or white powder paint.
- Meets PCI DSS (Payment Card Industry Data Security Standard) compliance requirements, when door installed.
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

Accessories

- Cable Managers
- Two Post Sliding Rack Shelf
- Fan Kits
- Grounding & Bonding
- Power Distribution Units (PDUs)
- Universal Rack Shelf
- Rack Unit Label
- Wall Rack Cabinet Sealing and Filter Kit
- Rack Screws with Pilot Point



30" Wide (Door not included)

Part No. Black	Part No. White	Overall Dimensions			Rack Units	Mounting (Usable) Dimensions		
		Height	Width	Depth		Height	Width	Depth
HWF3036U36BK	HWF3036U36WH	75.82	30.00	35.00	36U + 4U	63.00	19.00	33.50
HWF3042U36BK	HWF3042U36WH	86.32	30.00	35.00	42U + 6U	73.50	19.00	33.50
HWF3048U36BK	HWF3048U36WH	96.68	30.00	35.00	48U + 6U	84.00	19.00	33.50

Optional Doors

Compatible with Cabinet	Solid Door		Vented Door		Window Door	
	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.

Compatible with	Black	Solid Door	White	Black	Vented Door	White	Black	Window Door	White
Cabinet	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.
Height	Black	White	Black	White	Black	White	Black	White	White
36U	HWFSD3036UBK	HWFSD3036UWH	HWFVD3036UBK	HWFVD3036UWH	HWFWD3036UBK	HWFWD3036UWH			
42U	HWFSD3042UBK	HWFSD3042UWH	HWFVD3042UBK	HWFVD3042UWH	HWFWD3042UBK	HWFWD3042UWH			
48U	HWFSD3048UBK	HWFSD3048UWH	HWFVD3048UBK	HWFVD3048UWH	HWFWD3048UBK	HWFWD3048UWH			

Compatible Accessories

Compatible with	Part No.	Part No.	Vertical	Vertical Finger
Cabinet	Threaded 10-32	Square Hole	Cable	Cable Manager
Height			Tray	with Cover
36U	H1TRR36U30BK	H1SRR36U30BK	VCT63	-
42U	H1TRR42U30BK	H1SRR42U30BK	VCT73	H1VFMC3042UBK
48U	H1TRR48U30BK	H1SRR48U30BK	VCT85	H1VFMC3048UBK

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.