



Quality Products. Service Excellence.

Formed Steel Rack Panels *PBFS Series*

Also referred to as a Spacer Blank Panel

Features



- Constructed of 16-gauge steel.
- Fits standard EIA compliant rails.
- Install in unused rack space to improve both cooling efficiency and prevent air re-circulation.
- Finished in smooth powder paint.
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

Accessories



- Mounting Hardware



Part No. Gloss Black	Part No. Matte Black	Part No. ASA 61 Gray	Part No. RAL 7035 Light Gray	Part No. Matte White	Panel Height	Rack Units	Number of Mounting Slots
PBFS19000BK2	PBFS19000BK	-	-	-	0.09	1/2U	2
PBFS19001BK2	PBFS19001BK	PBFS19001GY2	PBFS19001LG2	PBFS19001WH	1.75	1U	4
PBFS19003BK2	PBFS19003BK	PBFS19003GY2	PBFS19003LG2	PBFS19003WH	3.50	2U	4
PBFS19005BK2	PBFS19005BK	PBFS19005GY2	PBFS19005LG2	PBFS19005WH	5.25	3U	4
PBFS19007BK2	PBFS19007BK	PBFS19007GY2	PBFS19007LG2	PBFS19007WH	7.00	4U	4
PBFS19008BK2	-	PBFS19008GY2	PBFS19008LG2	PBFS19008WH	8.75	5U	4
PBFS19010BK2	-	PBFS19010GY2	PBFS19010LG2	PBFS19010WH	10.50	6U	8
PBFS19012BK2	-	PBFS19012GY2	PBFS19012LG2	PBFS19012WH	12.25	7U	8
PBFS19014BK2	-	PBFS19014GY2	PBFS19014LG2	PBFS19014WH	14.00	8U	8
PBFS19015BK2	-	PBFS19015GY2	PBFS19015LG2	PBFS19015WH	15.75	9U	8
PBFS19017BK2	-	PBFS19017GY2	PBFS19017LG2	PBFS19017WH	17.50	10U	8
PBFS19019BK2	-	PBFS19019GY2	PBFS19019LG2	PBFS19019WH	19.25	11U	8
PBFS19021BK2	-	PBFS19021GY2	-	PBFS19021WH	21.00	12U	8
PBFS19022BK2	-	PBFS19022GY2	PBFS19022LG2	PBFS19022WH	22.75	13U	8
PBFS19024BK2	-	PBFS19024GY2	-	PBFS19024WH	24.50	14U	10
PBFS19026BK2	-	PBFS19026GY2	-	PBFS19026WH	26.25	15U	10
PBFS19028BK2	-	PBFS19028GY2	-	PBFS19028WH	28.00	16U	12

Part No.	Part No.	Part No.	Part No.	Part No.		Rack	Number of
Gloss Black	Matte Black	ASA 61 Gray	RAL 7035 Light Gray	Matte White	Panel Height	Units	Mounting Slots
PBFS19029BK2	-	PBFS19029GY2	-	PBFS19029WH	29.75	17U	12
PBFS19031BK2	-	PBFS19031GY2	-	PBFS19031WH	31.50	18U	12

Tags: **Flanged, Folded**

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.