



Quality Products. Service Excellence.

Polycarbonate HMI Hinged Cover Kits *PJHMI Series*



Features

- Provides protection for instruments or electronics requiring routine attention or detail.
- Available in light gray solid opaque or polycarbonate thermoplastic clear covers.
- Cover Latching Options - hinged screw cover, tamper proof screw cover, and snap latch with pad lock feature.
- Listed UL component for use with enclosures rated NEMA Types 1, 3, 3R, 4, 4X, 12 or 13.
- CSA listed NEMA Type 1, 3, 3R, 4, 4X, 12 or 13.
- 316 stainless steel hinge pin.
- UV stabilized for outdoor use.
- Formed-In-Place (FIP) polyurethane gasket in continuous channel.
- Designed for use with wall thicknesses from 16 gauge through 1/4"
- #10-32 threaded brass inserts with plated steel mounting fasteners.
- Service temperature -31°F (-35°C) to 266°F (130°C)

Accessories

- HMI Cover Prop Arm



Clear Cover	Opaque Cover	Optional Prop Arm	Closure Style	Frame Size Dimensions			Viewing Area	
				H	W	D	H	W
PJHMI66CCH	PJHMI66H	PJHMI66PROP	Screw Cover	6.50	6.72	2.27	4.47	4.69
PJHMI66CCHTP	PJHMI66HTP	PJHMI66PROP	Tamperproof Screw Cover	6.50	6.72	2.27	4.47	4.69
PJHMI66CCL	PJHMI66L	PJHMI66PROP	Snap Latch Cover	6.50	6.72	2.27	4.47	4.69
PJHMI86CCH	PJHMI86H	PJHMI86PROP	Screw Cover	8.50	6.72	2.27	6.47	4.69
PJHMI86CCHTP	PJHMI86HTP	PJHMI86PROP	Tamperproof Screw Cover	8.50	6.72	2.27	6.47	4.69
PJHMI86CCL	PJHMI86L	PJHMI86PROP	Snap Latch Cover	8.50	6.72	2.27	6.47	4.69

Clear Cover	Opaque Cover	Optional Prop Arm	Closure Style	Frame Size Dimensions			Viewing Area	
				H	W	D	H	W
PJHMI88CCH	PJHMI88H	PJHMIPROP88	Screw Cover	7.93	8.15	2.27	6.47	6.69
PJHMI88CCHTP	PJHMI88HTP	PJHMIPROP88	Tamperproof Screw Cover	7.93	8.15	2.27	6.47	6.69
PJHMI88CCL	PJHMI88L	PJHMIPROP88	Snap Latch Cover	7.93	8.15	2.27	6.47	6.69
PJHMI108CCH	PJHMI108H	PJHMIPROP108	Screw Cover	9.93	8.15	2.27	8.47	6.69
PJHMI108CCHTP	PJHMI108HTP	PJHMIPROP108	Tamperproof Screw Cover	9.93	8.15	2.27	8.47	6.69
PJHMI108CCL	PJHMI108L	PJHMIPROP108	Snap Latch Cover	9.93	8.15	2.27	8.47	6.69
PJHMI1210CCH	PJHMI1210H	PJHMIPROP1210	Screw Cover	11.93	10.15	2.27	10.47	8.69
PJHMI1210CCHTP	PJHMI1210HTP	PJHMIPROP1210	Tamperproof Screw Cover	11.93	10.15	2.27	10.47	8.69
PJHMI1210CCL	PJHMI1210L	PJHMIPROP1210	Snap Latch Cover	11.93	10.15	2.27	10.47	8.69
PJHMI1412CCH	PJHMI1412H	PJHMIPROP1412	Screw Cover	13.95	12.07	2.20	12.49	10.71
PJHMI1412CCHTP	PJHMI1412HTP	PJHMIPROP1412	Tamperproof Screw Cover	13.95	12.07	2.20	12.49	10.71
PJHMI1412CCL	PJHMI1412L	PJHMIPROP1412	Snap Latch Cover	13.95	12.07	2.20	12.49	10.71
PJHMI1614CCH	PJHMI1614H	PJHMIPROP1614	Screw Cover	16.01	14.23	2.27	14.49	12.71
PJHMI1614CCHTP	PJHMI1614HTP	PJHMIPROP1614	Tamperproof Screw Cover	16.01	14.23	2.27	14.49	12.71
PJHMI1614CCL	PJHMI1614L	PJHMIPROP1614	Snap Latch Cover	16.01	14.23	2.27	14.49	12.71
PJHMI2016CCH	PJHMI2016H	PJHMIPROP2016	Screw Cover	20.50	16.72	2.27	18.49	14.71
PJHMI2016CCHTP	PJHMI2016HTP	PJHMIPROP2016	Tamperproof Screw Cover	20.50	16.72	2.27	18.49	14.71
PJHMI2016CCL	PJHMI2016L	PJHMIPROP2016	Snap Latch Cover	20.50	16.72	2.27	18.49	14.71

Tags: **window kit hinged***Data subject to change without notice*

© 2021. Hammond Manufacturing Ltd. All rights reserved.