



Quality Products. Service Excellence.

Luran Water-Tight Enclosures R285 Series

technoDISC



Key Features:

- Premium plastic, UV-resistant, Luran enclosures for outdoor applications
- Shallow lid, deep body
- Captive, stainless steel - lid screws
- Enclosure can be mounted to wall or shelf after closing the lid
- Integrated 1.7 mm recess in lid for membrane keypads and front panels
- Silicone gasket standard (-50°C up to +140°C)
- Degree of protection: IP 66
- Enclosure is a light grey, RAL 7035 Luran - UL 94 HB flammability rating
- Clip-on design covers, plastic polyoxymethylene (POM), anthracite grey, RAL 7016



Features:



Snap in design covers hide both lid screws and installation holes.



Integrated recesses for membrane keypads.



Enclosure can be installed after closing lid.



Standoffs in the enclosure and lid for panels, P.C. boards & components.

Part Number	Length	Width	Depth (Including Lid)
R285-080-000	110	97	55
R285-100-000	130	119	65
R285-120-000	150	139	80
R285-160-000	190	179	90

© 2021. Hammond Manufacturing Ltd. All rights reserved.