



Quality Products. Service Excellence.

2-Post Open Frame Rack *RB-2PA Series*

1,500 lbs (680 kg) Weight Capacity

Features:

- Constructed of 5052H32 aluminum rails.
- EIA compliant 12-24 double-tapped rails.
- Numbered rail markings.
- Side ganging and accessory mounting hole provisions.
- Knockdown self-squaring design ships unassembled for easy handling and shipping protection.
- Includes a 30-pack of 12-24 mounting hardware.
- Available in either anodized natural satin or black finish.
- Load rated to 1,500 lbs (680 kg) of equipment load capacity.
- RoHS Compliant.



RACK BASICS®



Part of the Rack Basics® line of economy rack solutions

Accessories

- High-Density Vertical Finger Manager with Slam-Latching Door
- Vertical Finger Cable Manager with Door
- Top Wire Management
- Horizontal Finger Cable Manager
- Universal Rack Shelf
- Two Post Mounting Deep Channel Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- 2-Post Rack Low Profile Dolly
- Rack Isolation Kit
- 12-24 Mounting Hardware
- Vertical Rack Cable Manager with Door
- Vertical Cable Manager Extensions
- Horizontal Ring Cable Manager
- Rack Panels
- Two Post Mounting Adjustable Shelf
- Two Post Centered Shelf
- Two-Post Extension Support Bracket
- Open Frame Rack and Rack Cabinet Joining Kit
- Grounding & Bonding
- PDUs and Outlet Strips

Part No. Black	Part No. Natural Finish	Overall Dimensions			Rack Units	Mounting Dimensions	
		Height	Width	Depth		Height	Width
RB-2PA1945BK	RB-2PA1945NF	83.90	20.25	15.00	45U	78.75	19.00
RB-2PA2345BK	-	83.90	24.25	15.00	45U	78.75	23.00

Tags: Relay Rack, H-Frame, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack, *Data subject to change without notice*
Two-Post Rack, knock-down, knock down, rb2pa

© 2021. Hammond Manufacturing Ltd. All rights reserved.

