



Quality Products. Service Excellence.

Open Frame Wall Rack *RB-2PW Series*

Up to 200 lbs (91 kg) Weight Capacity



Features

- The rails are constructed in 12-gauge steel while the body is constructed in 14-gauge steel.
- EIA compliant 10-32 tapped rails with 19" mounting and rack unit indicators.
- Provides 18 inches of usable depth.
 - Optional **RB-2PW-EXT** extender can be used to add up to 7" of usable mounting depth while maintaining the load capacity.
- Open-rear design can be installed over existing equipment.
- Finished in smooth black powder paint.
- Knockdown design ships unassembled for easy handling and shipping protection.
- Includes starter pack of **SCREW1032-25** screws.
- Tested up to nearly double the suggested load rating of 200 lbs (90.72 kg).
- TAA Compliant.
- RoHS Compliant.
- Manufactured in North America.



Need a different height? Purchase our 8U version and the desired height of our **URR Rack Rails** (Add 4U to the desired height). Note we only approve the weight capacity up to 20U.

Accessories

- Cable Managers
- Two Post Mounting Adjustable Shelf
- Two Post Mounting Clamping Shelf
- Rack Panels
- Universal Rack Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- Hinged Clear Security Cover
- PDUs and Outlet Strips
- Adjustable Rack Mount DIN Rail Kit



Part No.	Overall Dimensions	Rack	Mounting Dimensions	Weight
----------	--------------------	------	---------------------	--------

Part No.	Height	Overall Width	Dimensions	Depth	Units	Height	Mounting Width	Dimensions	Depth	Capacity
	Height		Width	Depth	Units	Height		Width	Depth	Capacity
RB-2PW8	18.00		20.00	18.00	8U	14.00		19.00	18.00	200 lbs
RB-2PW12	28.50		20.00	18.00	12U	21.00		19.00	18.00	200 lbs
RB-2PW20	40.00		20.00	18.00	20U	35.00		19.00	18.00	175 lbs

Optional Extender Bracket

Part No.	Description
RB-2PW-EXT	Provides additional seven inches of mounting depth (18" to 25") while maintaining weight load capacity.

Data subject to change without notice