



Quality Products. Service Excellence.

Horizontal Finger Cable Manager *RB-HFM Series*

Features:



- Metal components constructed in 16-gauge steel.
- Three (3) inch length fingers constructed in black plastic.
- Snap-on, hinged door.
- Includes cutouts at rear for cable pass-through.
- Fits standard EIA compliant mounting rails.
- Metal components finished in textured black powder paint.
- Requires mounting hardware.
- RoHS and REACH compliant.

Part of the Rack Basics® line of economy rack solutions.

Accessories



- Mounting Hardware
- Hook and Loop Roll



Part No.	Overall Dimensions			Usable Mounting Dimensions	
	Height	Width	Depth	Rack Units	Height
RB-HFM1	1.72	19.00	4.37	1U	1.75
RB-HFM2	3.22	19.00	4.37	2U	3.50

Note that two (2) of the RB-HFM1 cannot be installed on top of each other as the hinged door clip will interfere with the other unit.

Estimated Cable Fill Capacities

Rack Units	Description	Recommended Cable Fill (50% Fill Ratio)		Maximum Cable Fill (100% Fill Ratio)	
		Cat 6	Cat 6a	Cat 6	Cat 6a
1U	Channel Opening	20	14	40	28
	Finger Opening	18	12	35	24
	Rear Pass Through	20	14	40	28
2U	Channel Opening	49	34	99	69
	Finger Opening	18	12	35	24
	Rear Pass Through	39	27	77	54

Deeper Version (TAA Compliant)

Part No.	Overall Dinmensions			Usable Mounting Dimensions	
	Height	Width	Depth	Rack Units	Height
RB-HFMD1	1.47	19.00	6.50	1U	1.75
RB-HFMD2	3.22	19.00	6.50	2U	3.50
RB-HFMD3	5.22	19.00	6.50	3U	5.25
RB-HFMD4	6.97	19.00	6.50	4U	7.00

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.