



*Quality Products. Service Excellence.*

## Vertical Cable Manager with Door *RRCM Series*

For use with Open Frame Racks



Vertical cable managers facilitate cable organization for a single or multiple rack installation. The RRCM Series includes a magnetic hinged door that hides cables and improves the esthetics of the installation. The RRCM includes strong cross bars to support your heavy duty cable applications.

### Features

- All-steel construction with side and rear cut-outs for cable pass-through.
- Includes cable mounting lances for hook and loop cable organization.
- Mounts to either side of open frame rack (includes mounting hardware).
- Attached hinged door opens to one side and secures closed with a magnetic strip.
- Can be used with top wire management accessories below (excludes RRAL Series).
- Manager body and door are constructed of 16-gauge steel.
- Manager and door finished in textured black power coat finish.
- RoHS Compliant.
- Manufactured in North America.

### Compatibility

- Designed specifically for the DNRR\*HDW but also compatible with:
- DRZ4 Series
- RB-2P Series
- DC4R Series



You may consider our **RB-VCM** Series vertical cable manager. [Learn more.](#)

### Accessories

- Vertical Cable Manager Extensions
- Hook and Loop Roll
- Top Wire Management



| Part No.   | Overall Dimensions |       |       | Mounting Dimensions |            | Door Included | Managers Included | Optional Chimney Part No. |
|------------|--------------------|-------|-------|---------------------|------------|---------------|-------------------|---------------------------|
|            | Height             | Width | Depth | Height              | Rack Units |               |                   |                           |
| RRCM44UD   | 82.00              | 6.00  | 5.00  | 77.00               | 44U        | Yes           | 1                 | RRCMCH65                  |
| RRCM48UD   | 89.00              | 6.00  | 5.00  | 84.00               | 48U        | Yes           | 1                 | RRCMCH65                  |
| RRCM844UD  | 82.00              | 8.00  | 6.00  | 77.00               | 44U        | Yes           | 1                 | RRCMCH86                  |
| RRCM848UD  | 89.00              | 8.00  | 6.00  | 84.00               | 48U        | Yes           | 1                 | RRCMCH86                  |
| RRCM1244UD | 82.00              | 12.00 | 6.00  | 77.00               | 44U        | Yes           | 1                 | n/a                       |

77 inch part numbers are also compatible with 78.75 (45U)

### Estimated Cable Fill Capacities

| Part No. | Description | Opening | Recommended Cable Fill (50% Fill Ratio) | Maximum Cable Fill (100% Fill Ratio) |
|----------|-------------|---------|-----------------------------------------|--------------------------------------|
|----------|-------------|---------|-----------------------------------------|--------------------------------------|

| Part No.   | Description       | Quantity    | Recommended Cable Fill (50% Cat 6 Ratio) | Recommended Cable Fill (50% Cat 6a Ratio) | Maximum Cable Fill (100% Cat 6 Ratio) | Maximum Cable Fill (100% Cat 6a Ratio) |
|------------|-------------------|-------------|------------------------------------------|-------------------------------------------|---------------------------------------|----------------------------------------|
|            |                   | Quantity    | Cat 6                                    | Cat 6a                                    | Cat 6                                 | Cat 6a                                 |
| RRCM44UD   | Channel Opening   | 1           | 149                                      | 103                                       | 297                                   | 207                                    |
|            | Side Opening      | 2 x 19 = 38 | 31                                       | 21                                        | 61                                    | 42                                     |
|            | Rear Pass Through | 10          | 28                                       | 19                                        | 55                                    | 38                                     |
| RRCM48UD   | Channel Opening   | 1           | 149                                      | 103                                       | 297                                   | 207                                    |
|            | Side Opening      | 2 x 21 = 42 | 31                                       | 21                                        | 61                                    | 42                                     |
|            | Rear Pass Through | 11          | 28                                       | 19                                        | 55                                    | 38                                     |
| RRCM844UD  | Channel Opening   | 1           | 226                                      | 157                                       | 452                                   | 314                                    |
|            | Side Opening      | 2 x 19 = 38 | 31                                       | 21                                        | 61                                    | 42                                     |
|            | Rear Pass Through | 10          | 28                                       | 19                                        | 55                                    | 38                                     |
| RRCM848UD  | Channel Opening   | 1           | 226                                      | 157                                       | 452                                   | 314                                    |
|            | Side Opening      | 2 x 21 = 42 | 31                                       | 21                                        | 61                                    | 42                                     |
|            | Rear Pass Through | 11          | 28                                       | 19                                        | 55                                    | 38                                     |
| RRCM1244UD | Channel Opening   | 1           | 341                                      | 237                                       | 681                                   | 473                                    |
|            | Side Opening      | 2 x 19 = 38 | 31                                       | 21                                        | 61                                    | 42                                     |
|            | Rear Pass Through | 2 x 10 = 20 | 28                                       | 19                                        | 55                                    | 38                                     |

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.