



Quality Products. Service Excellence.

Chassis Sliding Rack Rail Kit *RSLIDE Series*

Adjustable sliding rail kit for chassis. The perfect DIY solution for allowing equipment to rackmount and slide.



Features

- Heavy duty double rail, ball bearing type equipment slides.
- Adjustable depth.
- Sold in pairs.
- Mounts two (2) pairs of 19" mounting rails.
- Rack mounting hardware sold separately.
- Supports up to 16.64" equipment width between the slides.
- The slides feature a stopping mechanism, preventing the shelf from accidentally falling out of the slide tray.
- Up to 145 lbs (65 kg) in weight capacity.
 - Slides are tested to BIFMA Standards with load capacity @ 12 times/minute for 55000 cycles minimum.
- Zinc plated finish.
- RoHS Compliant.
- Manufactured in North America.

Gallery



Accessories

- Extender Bracket for Sliding Shelves
- Mounting Hardware

Part No.	Overall Dimensions		Mounting Dimensions		Internal Equipment	Suggested
	Length	Slide Travel	Min Depth	Max Depth	Width	Load Rating (Extended)
RSLIDE12	12.00	12.00	10.28	14.90	16.64	145 lbs
RSLIDE16	16.00	16.00	14.00	18.60	16.64	130 lbs
RSLIDE22	22.00	22.00	20.30	24.90	16.64	107 lbs
RSLIDE26	26.00	26.00	23.75	27.60	16.64	94 lbs
RSLIDE28	28.00	28.00	23.80	30.70	16.64	85 lbs

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.

