



Quality Products. Service Excellence.

High-Density Vertical Finger Manager with Slam-Latching Door **VFM**

Series

For use with Open Frame Racks



The new Hammond Vertical Fingered Manager (VFM) is designed to manage easy to install, double-hinged door keeps the rack system visually organized and can be removed for ease of cable installation.

Features

- Sturdy, reversible steel slam-latch door/cover with pinch-trigger handle included.
- Available in:
 - Four (4) widths (6", 8", 10" or 12").
 - Two (2) powder coat finished (textured black and textured white).
- Metal finger features sturdy T-shape steel fingers are spaced at 2RU and provide support for high-density cable bundles and heavy gauge cables. Includes clip-on plastic finger guards (shipped loose) for cable 1.25" bend radius.
- Each manager comes with two openings for cable pass-thru.
- Includes cable mounting lances for hook and loop cable organization.
- Compatible with Hammond **DNRRHDW**, **DC4R**, **DRZ4**, **RB-2P** and **RB-2PA** Series of open frame racks.
 - Use the optional riser base **VFMB2BK** for easier installation and manager support.
 - We strongly recommend you use our **rack bolt-down kit** when mounting large cable managers.
- Optional inner and side panel, spool and cable divider accessories available.
- TAA Compliant.
- RoHS Compliant.
- Manufactured in North America.

Gallery



Accessories



Double-Sided (Steel Fingers with Plastic Radius)

Part No. Black	Part No. White	Overall Dimensions (Inches)			Mounting Dimensions		Door Included
		Height	Width	Depth	Units	Rack Units	
VFMMD6BK	VFMMD6WH	81.00	6.00	24.50	77.00	44	Yes
VFMMD8BK	VFMMD8WH	81.00	8.00	24.50	77.00	44	Yes
VFMMD10BK	VFMMD10WH	81.00	10.00	24.50	77.00	44	Yes
VFMMD12BK	VFMMD12WH	81.00	12.00	24.50	77.00	44	Yes

VFM Specific Accessories

Description	6.00		8.00		10.00		12.00	
	Part No.		Part No.		Part No.		Part No.	
	Black	White	Black	White	Black	White	Black	White
Accessory Inner Panel	VFMAP6BK	VFMAP6WH	VFMAP8BK	VFMAP8WH	VFMAP10BK	VFMAP10WH	VFMAP12BK	VFMAP12WH

Description	6.00		8.00		10.00		12.00	
	Part No.		Part No.		Part No.		Part No.	
	Black	White	Black	White	Black	White	Black	White
Solid Inner Panel	VFMAP6BK	VFMAP6WH	VFMAP8BK	VFMAP8WH	VFMAP10BK	VFMAP10WH	VFMAP12BK	VFMAP12WH
	VFMFP6BK	VFMFP6WH	VFMFP8BK	VFMFP8WH	VFMFP10BK	VFMFP10WH	VFMFP12BK	VFMFP12WH
	VFMFP6BK	VFMFP6WH	VFMFP8BK	VFMFP8WH	VFMFP10BK	VFMFP10WH	VFMFP12BK	VFMFP12WH
Manager Side Panel	VFMSPBK	VFMSPWH	VFMSPBK	VFMSPWH	VFMSPBK	VFMSPWH	VFMSPBK	VFMSPWH

Estimated Cable Fill Capacities

Part No.	Description	Recommended Cable Fill (50% Fill Ratio)		Maximum Cable Fill (100% Fill Ratio)	
		Cat 6	Cat 6a	Cat 6	Cat 6a
VFMMD6BK	Channel Opening	467	324	993	648
	Finger Opening	74	52	149	103
	Rear Pass Through	387	269	774	538
VFMMD8BK	Channel Opening	700	486	1400	972
	Finger Opening	74	52	149	103
	Rear Pass Through	387	269	774	538
VFMMD10BK	Channel Opening	933	648	1866	1296
	Finger Opening	74	52	149	103
	Rear Pass Through	387	269	774	538
VFMMD12BK	Channel Opening	1166	810	2333	1620
	Finger Opening	74	52	149	103
	Rear Pass Through	387	269	774	538

Tags: **double-sided manager, double sided**

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.