



THREE PHASE, NEMA 3R STYLE ENCLOSURE

480 Delta Primary Volts 208Y/120 Secondary Volts 60 Hz

kVA	Catalog Number	Case Style (Page 250)	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall	Wiring Diagram (Pages 258-268)
			Width	Depth	Height			
2	P002KBKB	NQT3	12.38	5.44	12.39	49	W	SCD 8
3	P003KBKB	NQT3	12.38	5.44	12.39	68	W	SCD 8
6	P006KBKF	NQT4	15.19	6.94	16.39	146	W	SCD 8
9	P009KBKF	NQT5	16.63	10.25	17.89	211	W	SCD 8
15	P015KBKF	NQT6	19.25	10.44	17.89	270	W	SCD 7
30	P030KBKF	NQT7	20.25	13.00	23.38	555	F or W*	SCD 9
45	P045KBKF	NQT8	22.25	13.00	28.38	765	F or W*	SCD 9
75	P075KBKF	NQT9	31.25	16.00	29.88	1600	F	SCD 9
112.5	P112KBKF	NQT10	38.44	26.00	39.13	2100	F	SCD 9
150	P150KBKF	NQT11	37.38	30.00	45.63	2650	F	SCD 9

*WALL MOUNTING KIT REQUIRED. REFER TO PAGES 255 FOR DETAILS.

480 Delta Primary Volts 240 Delta Secondary Volts 60 Hz

kVA	Catalog Number	Case Style (Page 250)	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall	Wiring Diagram (Pages 258-268)
			Width	Depth	Height			
2	P002KDKB	NQT3	12.38	5.44	12.39	49	W	SCD 12
3	P003KDKB	NQT3	12.38	5.44	12.39	68	W	SCD 12
6	P006KDKF	NQT4	15.19	6.94	16.39	146	W	SCD 12
9	P009KDKF	NQT5	16.63	10.25	17.89	211	W	SCD 12
15	P015KDKF	NQT6	19.25	10.44	17.89	270	W	SCD 37
30	P030KDKF	NQT7	20.25	13.00	23.38	555	F or W*	SCD 38
45	P045KDKF	NQT8	22.25	13.00	28.38	765	F or W*	SCD 38
75	P075KDKF	NQT9	31.25	16.00	29.88	1600	F	SCD 38
112.5	P112KDKF	NQT10	38.44	26.00	39.13	2100	F	SCD 38
150	P150KDKF	NQT11	37.38	30.00	45.63	2650	F	SCD 38

*WALL MOUNTING KIT REQUIRED. REFER TO PAGES 255 FOR DETAILS.

600 Delta Primary Volts 208Y/120 Secondary Volts 60 Hz

kVA	Catalog Number	Case Style (Page 250)	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall	Wiring Diagram (Pages 258-268)
			Width	Depth	Height			
2	P002PBKB	NQT3	12.38	5.44	12.39	49	W	SCD 8
3	P003PBKB	NQT3	12.38	5.44	12.39	68	W	SCD 8
6	P006PBKF	NQT4	15.19	6.94	16.39	146	W	SCD 8
9	P009PBKF	NQT5	16.63	10.25	17.89	211	W	SCD 8
15	P015PBKF	NQT6	19.25	10.44	17.89	270	W	SCD 8
30	P030PBKF	NQT7	20.25	13.00	23.38	555	F or W*	SCD 9
45	P045PBKF	NQT8	22.25	13.00	28.38	765	F or W*	SCD 9
75	P075PBKF	NQT9	31.25	16.00	29.88	1600	F	SCD 9
112.5	P112PBKF	NQT10	38.44	26.00	39.13	2100	F	SCD 9
150	P150PBKF	NQT11	37.38	30.00	45.63	2650	F	SCD 9

*WALL MOUNTING KIT REQUIRED. REFER TO PAGES 255 FOR DETAILS.

SECTION 9

