

THREE PHASE, NEMA 3R STYLE ENCLOSURE



600 Wye Primary Volts 240 Delta Secondary Volts 60 Hz

kVA	Catalog Number	Case Style (Page 250)	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall	Wiring Diagram (Pages 258-268)
			Width	Depth	Height			
2	P002PDKB	NQT3	12.38	5.44	12.39	49	W	SCD 27
3	P003PDKB	NQT3	12.38	5.44	12.39	68	W	SCD 27
6	P006PDKF	NQT4	15.19	6.94	16.39	146	W	SCD 27
9	P009PDKF	NQT5	16.63	10.25	17.89	211	W	SCD 29
15	P015PDKF	NQT6	19.25	10.44	17.89	270	W	SCD 29

600 Delta Primary Volts 380Y/220 Secondary Volts 60 Hz

kVA	Catalog Number	Case Style (Page 250)	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall	Wiring Diagram (Pages 258-268)
			Width	Depth	Height			
2	P002PGKB	NQT3	12.38	5.44	12.39	49	W	SCD 8
3	P003PGKB	NQT3	12.38	5.44	12.39	68	W	SCD 8
6	P006PGKF	NQT4	15.19	6.94	16.39	146	W	SCD 8
9	P009PGKF	NQT5	16.63	10.25	17.89	211	W	SCD 8
15	P015PGKF	NQT6	19.25	10.44	17.89	270	W	SCD 8

600, 480 Delta Primary Volts 480Y/277 Secondary Volts 60 Hz

kVA	Catalog Number	Case Style (Page 250)	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall	Wiring Diagram (Pages 258-268)
			Width	Depth	Height			
2	P002QKKB	NQT3	12.38	5.44	12.39	49	W	SCD 20
3	P003QKKB	NQT3	12.38	5.44	12.39	68	W	SCD 20
6	P006QKKF	NQT4	15.19	6.94	16.39	146	W	SCD 20
9	P009QKKF	NQT5	16.63	10.25	17.89	211	W	SCD 3
15	P015QKKF	NQT7	20.25	13.00	23.38	380	F or W*	SCD 3
30	P030QKKF	NQT7	20.25	13.00	23.38	555	F or W*	SCD 11
45	P045QKKF	NQT8	22.25	13.00	28.38	765	F	SCD 11
75	P075QKKF	NQT9	31.25	16.00	29.88	1600	F	SCD 11
112.5	P112QKKF		Consult Factory					
150	P150QKKF		Consult Factory					

*WALL MOUNTING KIT REQUIRED. REFER TO PAGES 255 FOR DETAILS.

600 Delta Primary Volts 600Y/347 Secondary Volts 60 Hz

kVA	Catalog Number	Case Style (Page 250)	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall	Wiring Diagram (Pages 258-268)
			Width	Depth	Height			
2	P002PPKB	NQT3	12.38	5.44	12.39	49	W	SCD 8
3	P003PPKB	NQT3	12.38	5.44	12.39	68	W	SCD 8
6	P006PPKF	NQT4	15.19	6.94	16.39	146	W	SCD 8
9	P009PPKF	NQT5	16.63	10.25	17.89	211	W	SCD 8
15	P015PPKF	NQT6	19.25	10.44	17.89	270	W	SCD 8

SECTION 9

