

SINGLE PHASE, NEMA 3R STYLE ENCLOSURE



Export Model

190/200/208/220 X 380/400/415/440 Primary Volts 120/240 Secondary Volts 50/60 Hz

kVA	Catalog Number	Case Style <small>(Page 249)</small>	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall	Wiring Diagram <small>(Pages 258-268)</small>
			Width	Depth	Height			
0.05	QC05XECB	NQ0	3.75	5.25	7.25	7	W	SCD 28
0.10	QC10XECB	NQ0	3.75	5.25	7.25	8	W	SCD 28
0.15	QC15XECB	NQ0	3.75	5.25	7.25	11	W	SCD 28
0.20	QC20XECB	NQ1	4.50	5.75	7.25	13	W	SCD 28
0.25	QC25XECB	NQ1	4.50	5.75	7.25	14	W	SCD 28
0.35	QC35XECB	NQ1	4.50	5.75	7.25	15	W	SCD 28
0.50	QC50XECB	NQ2	5.00	4.75	9.25	18	W	SCD 28
0.75	QC75XEKB	NQ2	5.00	4.75	9.25	20	W	SCD 28
1	Q1C0XEKB	NQ3	5.88	5.50	10.00	26	W	SCD 28
1.5	Q1C5XEKF	NQ3	5.88	5.50	10.00	32	W	SCD 28
2	Q002XEKF	NQ4	7.00	6.50	11.25	52	W	SCD 28
3	Q003XEKF	NQ5	10.00	7.75	17.25	65	W	SCD 28
5	Q005XEKF	NQ5	10.00	7.75	17.25	105	W	SCD 28
7.5	Q007XEKF	NQ6	12.25	9.25	20.88	145	W	SCD 28
10	Q010XEKF	NQ6	12.25	9.25	20.88	195	W	SCD 28

For shielded units up to 0.50 kVA, replace the suffix "CB" with a "KB".

The above export model units carry the CE Mark.

