


# GENERAL INFORMATION

## NEMA 3R ENCLOSURE DIMENSIONAL DRAWINGS


### 'NJ' SERIES ENCLOSURES



| Case Style | Dimensions in Inches |       |       |       |       |      |      |      |       |      |       |       |       |
|------------|----------------------|-------|-------|-------|-------|------|------|------|-------|------|-------|-------|-------|
|            | A                    | B     | B'    | C     | D     | E    | F    | G    | H     | L    | M     | MA    | MB    |
| NJ1        | 39.50                | 34.00 | 30.00 | 51.50 | 35.50 | 6.00 | 8.00 | 4.00 | 7.75  | 1.00 | 34.00 | 24.00 | 32.00 |
| NJ2        | 48.50                | 38.40 | 34.00 | 59.00 | 40.00 | 8.00 | 8.00 | 4.00 | 10.50 | 1.00 | 38.00 | 27.50 | 36.00 |
| NJ4        | 32.00                | 32.50 | 28.50 | 50.00 | 34.00 | 8.00 | 8.00 | 4.00 | 5.00  | 1.00 | 32.50 | 22.00 | 30.50 |

Note: Mounting hole dimension is 0.69" diameter.

OPTIONAL NEMA 4, 12 AND STAINLESS STEEL ENCLOSURES ARE AVAILABLE.  
SEE PAGE 252 & 253 FOR DETAILS.



| Case Style | Dimensions in Inches |       |       |       |       |       |      |      |       |      |       |       |       |
|------------|----------------------|-------|-------|-------|-------|-------|------|------|-------|------|-------|-------|-------|
|            | A                    | B     | B'    | C     | D     | E     | F    | G    | H     | L    | M     | MA    | MB    |
| NJ3        | 51.50                | 43.40 | 39.00 | 66.00 | 47.00 | 10.00 | 8.00 | 4.00 | 8.75  | 1.00 | 43.00 | 34.00 | 41.00 |
| NJ6        | 64.00                | 44.40 | 40.00 | 71.00 | 50.00 | 11.50 | 9.00 | 5.00 | 12.00 | 1.00 | 44.00 | 40.00 | 42.00 |
| NJ7        | 64.00                | 51.40 | 47.00 | 75.00 | 54.00 | 11.50 | 9.00 | 5.00 | 12.00 | 1.00 | 51.00 | 40.00 | 49.00 |

Note: Mounting hole dimension is 0.69" diameter.

OPTIONAL NEMA 4, 12 AND STAINLESS STEEL ENCLOSURES ARE AVAILABLE.  
SEE PAGE 252 & 253 FOR DETAILS.

GENERAL INFORMATION

