

# Bundling and Securing

## Self-Affixing Cable Ties

### Screw Mount Cable Ties

#### Screw Mount Ties

PART NO.	TYPE	Mounting Screw Type	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width in. (mm)	Material	Color	Pkg. Qty.
T50ML0C2*	T50ML	#10 (M5)	50.0 (225.0)	15.4 (390.0)	4.0 (100.0)	0.2 (4.7)	PA66	Black	100
T50ML0M4*		#10 (M5)	50.0 (225.0)	15.4 (390.0)	4.0 (100.0)	0.2 (4.7)	PA66	Black	1000
T50ML9M4*		#10 (M5)	50.0 (225.0)	15.4 (390.0)	4.0 (100.0)	0.2 (4.7)	PA66	Natural	1000
T50ML9C2*		#10 (M5)	50.0 (225.0)	15.4 (390.0)	4.0 (100.0)	0.2 (4.7)	PA66	Natural	100
T50MR0C2*	T50MR	#10 (M5)	50.0 (225.0)	8.5 (215.0)	1.8 (45.0)	0.2 (4.7)	PA66	Black	100
T50MR0M4*		#10 (M5)	50.0 (225.0)	8.5 (215.0)	1.8 (45.0)	0.2 (4.7)	PA66	Black	1000
T50MR9M4*		#10 (M5)	50.0 (225.0)	8.5 (215.0)	1.8 (45.0)	0.2 (4.7)	PA66	Natural	1000
T50MR9X2*		#10 (M5)	50.0 (225.0)	8.5 (215.0)	1.8 (45.0)	0.2 (4.7)	PA66	Natural	25
T50MR0HSM4*		#10 (M5)	50.0 (225.0)	8.5 (215.0)	1.8 (45.0)	0.2 (4.7)	PA66	Black	1000
T50MR9C2*		#10 (M5)	50.0 (225.0)	8.5 (215.0)	1.8 (45.0)	0.2 (4.7)	PA66	Natural	100
T120MR0K2*	T120MR	1/4" (M6)	120.0 (535.0)	15.6 (395.0)	4.0 (102.0)	0.3 (7.6)	PA66	Black	50
T120MR0UVK2		1/4" (M6)	120.0 (535.0)	15.6 (395.0)	4.0 (102.0)	0.3 (7.6)	PA66HIRHSUV	Black	50
T120MR9K2*		1/4" (M6)	120.0 (535.0)	15.6 (395.0)	4.0 (102.0)	0.3 (7.6)	PA66	Natural	50
T120MR9H4*		1/4" (M6)	120.0 (535.0)	15.6 (395.0)	4.0 (102.0)	0.3 (7.6)	PA66	Natural	500
T120MR0H4*		1/4" (M6)	120.0 (535.0)	15.6 (395.0)	4.0 (102.0)	0.3 (7.6)	PA66	Black	500

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P. \*This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.