



Edge Clip Cable Ties

Cable Tie with Edge Clip

PART NO.	TYPE	Panel Thickness in. (mm)	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Material Cable Tie	Material Edge Clip	Color	Pkg. Qty.	Drawing
156-00556	T50REC23	0.12 – 0.24 (3.0 – 6.0)	50.0 (225)	8.0 (202.0)	2.0 (50.0)	PA66HS	PA66HIRHSUV	Black	500	
156-00592		0.12 – 0.24 (3.0 – 6.0)	50.0 (225)	8.0 (202.0)	2.0 (50.0)	PA66UV	PA66HIRHSUV	Black	100	
156-01162		0.12 – 0.24 (3.0 – 6.0)	50.0 (225)	8.0 (202.0)	2.0 (45.0)	PA66UV	PA66HIRHSUV	Black	500	
156-00567		0.12 – 0.24 (3.0 – 6.0)	50.0 (225)	8.0 (202.0)	2.0 (50.0)	PP	PA66HIRHSUV	Black	500	
156-00593	T50REC24	0.12 – 0.24 (3.0 – 6.0)	50.0 (225)	8.0 (202.0)	2.0 (50.0)	PA66UV	PA66HIRHSUV	Black	100	
156-00557		0.12 – 0.24 (3.0 – 6.0)	50.0 (225)	8.0 (202.0)	2.0 (50.0)	PA66UV	PA66HIRHSUV	Black	500	

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.
Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P.