

Edge Clip Cable Ties

Outside Serrated Cable Tie with Edge Clip

PART NO.	TYPE	Panel Thickness in. (mm)	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Material Cable Tie	Material Edge Clip	Color	Pkg. Qty.	Drawing
156-00862	T50ROSEC5B	0.04 – 0.12 (1.0 – 3.0)	50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	PA66HS	PA66HIRHS	Black	500	
156-00866	T50SOSEC9SD	0.04 – 0.12 (1.0 – 3.0)	50.0 (225.0)	6.0 (150.0)	1.4 (31.0)	PA66HS	PA66HIRHS	Black	500	
156-00867	T50ROSEC9	0.04 – 0.12 (1.0 – 3.0)	50.0 (225.0)	8.0 (200.0)	2.0 (45.0)	PA66HS	PA66HIRHS	Black	500	
156-00870	T50SOSEC10	0.04 – 0.12 (1.0 – 3.0)	50.0 (225.0)	6.0 (150.0)	1.4 (31.0)	PA66HS	PA66HIRHS	Black	500	
156-00871	T50ROSEC10	0.04 – 0.12 (1.0 – 3.0)	50.0 (225.0)	8.0 (200.0)	2.0 (45.0)	PA66HS	PA66HIRHS	Black	500	
156-04601	T50SOSEC19	0.12 – 0.24 (3.0 – 6.0)	50.0 (225.0)	6.0 (150.0)	1.4 (35.0)	PA66HS	PA66HIRHS	Black	500	
156-00872	T50ROSEC19	0.12 – 0.24 (3.0 – 6.0)	50.0 (225.0)	8.0 (200.0)	2.0 (45.0)	PA66HS	PA66HIRHS	Black	500	
156-00016	T50SOSEC20	0.12 – 0.24 (3.0 – 6.0)	50.0 (225.0)	6.0 (150.0)	1.4 (35.0)	PA66HS	PA66HIRHS	Black	500	
156-00873	T50ROSEC20	0.12 – 0.24 (3.0 – 6.0)	50.0 (225.0)	8.0 (200.0)	2.0 (45.0)	PA66HS	PA66HIRHS	Black	500	
156-00017	T50SOSEC21	0.04 – 0.12 (1.0 – 3.0)	50.0 (225.0)	6.0 (150.0)	1.4 (35.0)	PA66HS	PA66HIRHS	Black	500	
156-00874	T50ROSEC21	0.04 – 0.12 (1.0 – 3.0)	50.0 (225.0)	8.0 (200.0)	2.0 (45.0)	PA66HS	PA66HIRHS	Black	500	
156-00875	T50SOSEC22	0.04 – 0.12 (1.0 – 3.0)	50.0 (225.0)	6.0 (150.0)	1.4 (35.0)	PA66HS	PA66HIRHS	Black	500	
156-00876	T50ROSEC22	0.04 – 0.12 (1.0 – 3.0)	50.0 (225.0)	8.0 (200.0)	2.0 (45.0)	PA66HS	PA66HIRHS	Black	500	
156-00877	T50ROSEC23	0.12 – 0.24 (3.0 – 6.0)	50.0 (225.0)	8.0 (200.0)	2.0 (45.0)	PA66HS	PA66HIRHS	Black	500	
156-00878	T50ROSEC24	0.12 – 0.24 (3.0 – 6.0)	50.0 (225.0)	8.0 (200.0)	2.0 (45.0)	PA66HS	PA66HIRHS	Black	500	

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.
Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P.