


Ratchet P-Clamps

Size D - For bundle diameters from 1 3/8" to 2" (36.0 mm to 51.0 mm)

The Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables simply by using a flat-head screwdriver. This nondestructive release allows the clamp to be reused without removing or replacing any bolts or screws. The Ratchet P-Clamp is offered in four sizes and multiple mounting configurations.

Features and Benefits

- One-piece ratchet closure design allows for easy installation during pre- or final assembly.
- Four sizes and multiple configurations handle a wide range of diameters and applications, reducing part inventory.
- Clamp interior is designed to guide and center bundle to reduce pinching.
- Easy release feature allows for quick adjustments and maintenance.
- Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out.
- Steel mounting plate tolerates high torque mounting and is treated to resist chemicals and salt spray.



PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Mounting Hole Centers in. (mm)	Mounting Hole Dia. in. (mm)	Angle/Length	Length (L2) in. (mm)	Width (W) in. (mm)	Material	Pkg. Qty.
151-01664*	RCD15SM6	100.0 (445.0)	2.7 (69.1)	0.3 (6.5)	15 ° Short	4.6 (115.9)	1.4 (34.9)	PA66HIRHSUV, ST, ZN	160
151-01509*	RCD15SM8	100.0 (445.0)	2.7 (69.1)	0.3 (8.31)	15 ° Short	4.6 (115.9)	1.4 (34.9)	PA66HIRHSUV, ST, ZN	160
151-01510*	RCD15SM10	100.0 (445.0)	2.7 (69.1)	0.4 (10.29)	15 ° Short	4.6 (115.9)	1.4 (34.9)	PA66HIRHSUV, ST, ZN	160
151-01511*	RCD15SM12	100.0 (445.0)	2.7 (69.1)	0.5 (12.95)	15 ° Short	4.6 (115.9)	1.4 (34.9)	PA66HIRHSUV, ST, ZN	160
151-01666*	RCD30LM6	100.0 (445.0)	3.2 (80.5)	0.3 (6.5)	30 ° Long	5.0 (127.0)	1.4 (34.9)	PA66HIRHSUV, ST, ZN	140
151-01515*	RCD30LM8	100.0 (445.0)	3.2 (80.5)	0.3 (8.31)	30 ° Long	5.0 (127.0)	1.4 (34.9)	PA66HIRHSUV, ST, ZN	140
151-01516*	RCD30LM10	100.0 (445.0)	3.2 (80.5)	0.4 (10.29)	30 ° Long	5.0 (127.0)	1.4 (34.9)	PA66HIRHSUV, ST, ZN	140
151-01517*	RCD30LM12	100.0 (445.0)	3.2 (80.5)	0.5 (12.95)	30 ° Long	5.0 (127.0)	1.4 (34.9)	PA66HIRHSUV, ST, ZN	140
151-01665*	RCD30SM6	100.0 (445.0)	2.2 (55.9)	0.3 (6.5)	30 ° Short	4.0 (102.4)	1.4 (34.9)	PA66HIRHSUV, ST, ZN	160
151-01512*	RCD30SM8	100.0 (445.0)	2.2 (55.9)	0.3 (8.31)	30 ° Short	4.0 (102.4)	1.4 (34.9)	PA66HIRHSUV, ST, ZN	160
151-01513*	RCD30SM10	100.0 (445.0)	2.2 (55.9)	0.4 (10.29)	30 ° Short	4.0 (102.4)	1.4 (34.9)	PA66HIRHSUV, ST, ZN	160

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.
 *This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.