

Bundling and Securing

Clamps

Stainless Steel Ratchet P-Clamp

Size B - For bundle diameters from ½" to ¾" (12.7 mm to 19.5 mm)

PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Mounting Hole Centers in. (mm)	Mounting Hole Dia. in. (mm)	Angle/Length	Length (L2) in. (mm)	Width (W) in. (mm)	Material	Pkg. Qty.
151-01962*	RCB30SM12SS	100.0 (445.0)	1.9 (48.8)	0.5 (12.95)	30 ° Short	3.1 (78.5)	1.4 (34.9)	PA66HIRHSUV, SS304	280
151-01971*	RCB90LM6SS	100.0 (445.0)	1.1 (26.7)	0.3 (6.5)	90 ° Long	3.8 (96.8)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01972*	RCB90LM8SS	100.0 (445.0)	1.1 (26.7)	0.3 (8.31)	90 ° Long	3.8 (96.8)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01973*	RCB90LM10SS	100.0 (445.0)	1.1 (26.7)	0.4 (10.29)	90 ° Long	3.8 (96.8)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01974*	RCB90LM12SS	100.0 (445.0)	1.1 (26.7)	0.5 (12.95)	90 ° Long	3.8 (96.8)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01967*	RCB90SM6SS	100.0 (445.0)	1.1 (26.7)	0.3 (6.5)	90 ° Short	2.7 (68.8)	1.4 (34.9)	PA66HIRHSUV, SS304	280
151-01968*	RCB90SM8SS	100.0 (445.0)	1.1 (26.7)	0.3 (8.31)	90 ° Short	2.7 (68.8)	1.4 (34.9)	PA66HIRHSUV, SS304	280
151-01969*	RCB90SM10SS	100.0 (445.0)	1.1 (26.7)	0.4 (10.29)	90 ° Short	2.7 (68.8)	1.4 (34.9)	PA66HIRHSUV, SS304	280
151-01970*	RCB90SM12SS	100.0 (445.0)	1.1 (26.7)	0.5 (12.95)	90 ° Short	2.7 (68.8)	1.4 (34.9)	PA66HIRHSUV, SS304	280
151-01951*	RCB180LM6SS	100.0 (445.0)	4.1 (103.8)	0.3 (6.5)	180 ° Long	5.3 (134.1)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01952*	RCB180LM8SS	100.0 (445.0)	4.1 (103.8)	0.3 (8.31)	180 ° Long	5.3 (134.1)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01953*	RCB180LM10SS	100.0 (445.0)	4.1 (103.8)	0.4 (10.29)	180 ° Long	5.3 (134.1)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01954*	RCB180LM12SS	100.0 (445.0)	4.1 (103.8)	0.5 (12.95)	180 ° Long	5.3 (134.1)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01947*	RCB180MM6SS	100.0 (445.0)	2.9 (74.8)	0.3 (6.5)	180 ° Medium	4.1 (105.1)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01948*	RCB180MM8SS	100.0 (445.0)	2.9 (74.8)	0.3 (8.31)	180 ° Medium	4.1 (105.1)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01949*	RCB180MM10SS	100.0 (445.0)	2.9 (74.8)	0.4 (10.29)	180 ° Medium	4.1 (105.1)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01950*	RCB180MM12SS	100.0 (445.0)	2.9 (74.8)	0.5 (12.95)	180 ° Medium	4.1 (105.1)	1.4 (34.9)	PA66HIRHSUV, SS304	200
151-01943*	RCB180SM6SS	100.0 (445.0)	2.1 (52.8)	0.3 (6.5)	180 ° Short	3.3 (83.1)	1.4 (34.9)	PA66HIRHSUV, SS304	280
151-01944*	RCB180SM8SS	100.0 (445.0)	2.1 (52.8)	0.3 (8.31)	180 ° Short	3.3 (83.1)	1.4 (34.9)	PA66HIRHSUV, SS304	280
151-01945*	RCB180SM10SS	100.0 (445.0)	2.1 (52.8)	0.4 (10.29)	180 ° Short	3.3 (83.1)	1.4 (34.9)	PA66HIRHSUV, SS304	280
151-01946*	RCB180SM12SS	100.0 (445.0)	2.1 (52.8)	0.5 (12.95)	180 ° Short	3.3 (83.1)	1.4 (34.9)	PA66HIRHSUV, SS304	280

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

*This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.