

Bundling and Securing

Clamps

Stainless Steel Ratchet P-Clamp

Size D - For bundle diameters from 1 $\frac{3}{8}$ " to 2" (36.0 mm to 51.0 mm)

PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Mounting Hole Centers in. (mm)	Mounting Hole Dia. in. (mm)	Angle/Length	Length (L2) in. (mm)	Width (W) in. (mm)	Material	Pkg. Qty.
151-02026*	RCD30SM10SS	100.0 (445.0)	2.2 (55.9)	0.4 (10.29)	30 ° Short	4.0 (102.4)	1.4 (34.9)	PA66HIRHSUV, SS304	160
151-02027*	RCD30SM12SS	100.0 (445.0)	2.2 (55.9)	0.5 (12.95)	30 ° Short	4.0 (102.4)	1.4 (34.9)	PA66HIRHSUV, SS304	160
151-02036*	RCD90LM6SS	100.0 (445.0)	1.7 (42.4)	0.3 (6.5)	90 ° Long	4.6 (116.7)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02037*	RCD90LM8SS	100.0 (445.0)	1.7 (42.4)	0.3 (8.31)	90 ° Long	4.6 (116.7)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02038*	RCD90LM10SS	100.0 (445.0)	1.7 (42.4)	0.4 (10.29)	90 ° Long	4.6 (116.7)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02039*	RCD90LM12SS	100.0 (445.0)	1.7 (42.4)	0.5 (12.95)	90 ° Long	4.6 (116.7)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02032*	RCD90SM6SS	100.0 (445.0)	1.7 (42.4)	0.3 (6.5)	90 ° Short	3.5 (88.7)	1.4 (34.9)	PA66HIRHSUV, SS304	160
151-02033*	RCD90SM8SS	100.0 (445.0)	1.7 (42.4)	0.3 (8.31)	90 ° Short	3.5 (88.7)	1.4 (34.9)	PA66HIRHSUV, SS304	160
151-02034*	RCD90SM10SS	100.0 (445.0)	1.7 (42.4)	0.4 (10.29)	90 ° Short	3.5 (88.7)	1.4 (34.9)	PA66HIRHSUV, SS304	160
151-02035*	RCD90SM12SS	100.0 (445.0)	1.7 (42.4)	0.5 (12.95)	90 ° Short	3.5 (88.7)	1.4 (34.9)	PA66HIRHSUV, SS304	160
151-02016*	RCD180LM6SS	100.0 (445.0)	4.8 (121.0)	0.3 (6.5)	180 ° Long	6.6 (166.5)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02017*	RCD180LM8SS	100.0 (445.0)	4.8 (121.0)	0.3 (8.31)	180 ° Long	6.6 (166.5)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02018*	RCD180LM10SS	100.0 (445.0)	4.8 (121.0)	0.4 (10.29)	180 ° Long	6.6 (166.5)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02019*	RCD180LM12SS	100.0 (445.0)	4.8 (121.0)	0.5 (12.95)	180 ° Long	6.6 (166.5)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02012*	RCD180MM6SS	100.0 (445.0)	3.6 (92.0)	0.3 (6.5)	180 ° Medium	5.4 (137.5)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02013*	RCD180MM8SS	100.0 (445.0)	3.6 (92.0)	0.3 (8.31)	180 ° Medium	5.4 (137.5)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02014*	RCD180MM10SS	100.0 (445.0)	3.6 (92.0)	0.4 (10.29)	180 ° Medium	5.4 (137.5)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02015*	RCD180MM12SS	100.0 (445.0)	3.6 (92.0)	0.5 (12.95)	180 ° Medium	5.4 (137.5)	1.4 (34.9)	PA66HIRHSUV, SS304	140
151-02008*	RCD180SM6SS	100.0 (445.0)	2.8 (70.0)	0.3 (6.5)	180 ° Short	4.6 (115.5)	1.4 (34.9)	PA66HIRHSUV, SS304	160
151-02009*	RCD180SM8SS	100.0 (445.0)	2.8 (70.0)	0.3 (8.31)	180 ° Short	4.6 (115.5)	1.4 (34.9)	PA66HIRHSUV, SS304	160
151-02010*	RCD180SM10SS	100.0 (445.0)	2.8 (70.0)	0.4 (10.29)	180 ° Short	4.6 (115.5)	1.4 (34.9)	PA66HIRHSUV, SS304	160
151-02011*	RCD180SM12SS	100.0 (445.0)	2.8 (70.0)	0.5 (12.95)	180 ° Short	4.6 (115.5)	1.4 (34.9)	PA66HIRHSUV, SS304	160

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

*This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.