

Routing, Protection and Insulation

Wiring Duct

Slotted Wall Duct

Slotted Wall Wiring Duct

PART NO.	TYPE	Width (W) in. (mm)	Height (H) in. (mm)	Width (W2) in. (mm)	Width (W3) in. (mm)	Width (W4) in. (mm)	Width (W5) in. (mm)	Color	Pkg. Qty.
181-00554*	SL2X1	2.0 (50.8)	1.1 (26.9)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	0.8 (19.1)	Black	120 ft
181-21004*		2.0 (50.8)	1.1 (26.9)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	0.8 (19.1)	Gray	30 ft
181-21005*		2.0 (50.8)	1.1 (26.9)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	0.8 (19.1)	Gray	120 ft
181-21006*		2.0 (50.8)	1.1 (26.9)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	0.8 (19.1)	White	30 ft
181-21007*		2.0 (50.8)	1.1 (26.9)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	0.8 (19.1)	White	120 ft
181-22019*	SL2X2	2.0 (50.8)	2.1 (52.6)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	1.6 (40.6)	Black	30 ft
181-22020*		2.0 (50.8)	2.1 (52.6)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	1.6 (40.6)	Black	120 ft
181-22022*		2.0 (50.8)	2.1 (52.6)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	1.6 (40.6)	Gray	30 ft
181-22024*		2.0 (50.8)	2.1 (52.6)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	1.6 (40.6)	Gray	120 ft
181-22027*		2.0 (50.8)	2.1 (52.6)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	1.6 (40.6)	White	30 ft
181-22028*		2.0 (50.8)	2.1 (52.6)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	1.6 (40.6)	White	120 ft
181-23013*	SL2X3	2.0 (50.8)	3.1 (77.9)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	2.6 (66.0)	Black	30 ft
181-23003*		2.0 (50.8)	3.1 (77.9)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	2.6 (66.0)	Black	120 ft
181-23005*		2.0 (50.8)	3.1 (77.9)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	2.6 (66.0)	Gray	30 ft
181-23007*		2.0 (50.8)	3.1 (77.9)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	2.6 (66.0)	Gray	120 ft
181-23008*		2.0 (50.8)	3.1 (77.9)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	2.6 (66.0)	White	30 ft
181-23009*		2.0 (50.8)	3.1 (77.9)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	2.6 (66.0)	White	120 ft
181-24005*	SL2X4	2.0 (50.8)	4.1 (103.4)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	3.6 (91.4)	Black	30 ft
181-24003*		2.0 (50.8)	4.1 (103.4)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	3.6 (91.4)	Black	120 ft
181-24007*		2.0 (50.8)	4.1 (103.4)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	3.6 (91.4)	Gray	30 ft
181-24008*		2.0 (50.8)	4.1 (103.4)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	3.6 (91.4)	Gray	120 ft
181-24010*		2.0 (50.8)	4.1 (103.4)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	3.6 (91.4)	White	30 ft
181-24011*		2.0 (50.8)	4.1 (103.4)	2.0 (50.8)	0.4 (10.2)	1.0 (25.4)	3.6 (91.4)	White	120 ft

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.
For wire fill capacities and wiring duct material properties, see appendix. Sold in 6-ft. lengths. *This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.