

### Standard Cable Ties

#### T18R and T30R Series in Colors

PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width (W) in. (mm)	Material	Color	Pkg. Qty.
T30R6C2*	T30R	30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Blue	100
T30R6M4*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Blue	1000
T30R1C2*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Brown	100
T30R1M4*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Brown	1000
T30R8C2*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Gray	100
T30R8M4*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Gray	1000
T30R5C2*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Green	100
T30R5M4*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Green	1000
T30R3C2*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Orange	100
T30R3M4*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Orange	1000
T30R7C2*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Purple	100
T30R7M4*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Purple	1000
T30R2C2*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Red	100
T30R2M4*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Red	1000
T30R10C2*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	White	100
T30R10M4*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	White	1000
T30R4C2*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Yellow	100
T30R4M4*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66	Yellow	1000

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.  
 Installation tools: EVO7 and EVO7SP. \*This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.