

# Routing, Protection and Insulation

## Heat Shrink Tubing

### Non-Adhesive 2 to 1 Shrink Ratio

#### TFN21 Sticks Non-Adhesive Thin Wall

PART NO.	TYPE	Trade Size	Supplied Ø (D) in. (mm)	Recovered Ø (d) in. (mm)	Wall Thickness (WT) in. (mm)	Color	Pkg. Qty.
309-65174*	TFN21-ST 19.1/9.5	3/4	0.750 (19.1)	0.375 (9.5)	0.027 (0.7)	Black	5
309-65177*		3/4	0.750 (19.1)	0.375 (9.5)	0.027 (0.7)	Blue	5
309-65175*		3/4	0.750 (19.1)	0.375 (9.5)	0.027 (0.7)	Clear	5
309-65296*		3/4	0.750 (19.1)	0.375 (9.5)	0.027 (0.7)	Green	5
309-65176*		3/4	0.750 (19.1)	0.375 (9.5)	0.027 (0.7)	Red	5
309-65178*		3/4	0.750 (19.1)	0.375 (9.5)	0.027 (0.7)	White	5
309-65179*		3/4	0.750 (19.1)	0.375 (9.5)	0.027 (0.7)	Yellow	5
309-65184*	TFN21-ST 25.4/12.7	1	0.750 (25.4)	0.500 (12.7)	0.027 (0.9)	Black	5
309-65298*		1	1.000 (25.4)	0.500 (12.7)	0.034 (0.9)	Blue	5
309-65280*		1	1.000 (25.4)	0.500 (12.7)	0.034 (0.9)	Clear	5
309-65301*		1	1.000 (25.4)	0.500 (12.7)	0.034 (0.9)	Green	5
309-65297*		1	1.000 (25.4)	0.500 (12.7)	0.034 (0.9)	Red	5
309-65299*		1	1.000 (25.4)	0.500 (12.7)	0.034 (0.9)	White	5
309-65300*		1	1.000 (25.4)	0.500 (12.7)	0.034 (0.9)	Yellow	5
309-65271*	TFN21-ST 31.8/16.0	1-1/4	1.250 (31.8)	0.625 (16.0)	0.039 (1.0)	Black	10
309-65273*		1-1/4	1.250 (31.8)	0.625 (16.0)	0.039 (1.0)	Blue	10
309-65270*		1-1/4	1.250 (31.8)	0.625 (16.0)	0.039 (1.0)	Clear	10
309-65276*		1-1/4	1.250 (31.8)	0.625 (16.0)	0.039 (1.0)	Green	10
309-65272*		1-1/4	1.250 (31.8)	0.625 (16.0)	0.039 (1.0)	Red	10
309-65274*		1-1/4	1.250 (31.8)	0.625 (16.0)	0.039 (1.0)	White	10
309-65275*		1-1/4	1.250 (31.8)	0.625 (16.0)	0.039 (1.0)	Yellow	10
309-65194*	TFN21-ST 38.1/19.1	1-1/2	1.500 (38.1)	0.750 (19.1)	0.039 (1.0)	Black	6
309-65303*		1-1/2	1.500 (38.1)	0.750 (19.1)	0.039 (1.0)	Blue	6
309-65193*		1-1/2	1.500 (38.1)	0.750 (19.1)	0.039 (1.0)	Clear	6
309-65306*		1-1/2	1.500 (38.1)	0.750 (19.1)	0.039 (1.0)	Green	6
309-65302*		1-1/2	1.500 (38.1)	0.750 (19.1)	0.039 (1.0)	Red	6
309-65304*		1-1/2	1.500 (38.1)	0.750 (19.1)	0.039 (1.0)	White	6
309-65305*		1-1/2	1.500 (38.1)	0.750 (19.1)	0.039 (1.0)	Yellow	6
309-65211*	TFN21-ST 50.8/25.4	2	2.000 (50.8)	1.000 (25.4)	0.043 (1.1)	Black	6
309-65213*		2	2.000 (50.8)	1.000 (25.4)	0.043 (1.1)	Blue	6
309-65210*		2	2.000 (50.8)	1.000 (25.4)	0.043 (1.1)	Clear	6
309-65216*		2	2.000 (50.8)	1.000 (25.4)	0.043 (1.1)	Green	6
309-65212*		2	2.000 (50.8)	1.000 (25.4)	0.043 (1.1)	Red	6
309-65214*		2	2.000 (50.8)	1.000 (25.4)	0.043 (1.1)	White	6
309-65215*		2	2.000 (50.8)	1.000 (25.4)	0.043 (1.1)	Yellow	6

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

\*This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.