

Labels for Thermal Transfer Printers

Thermal Transfer Self-Laminating Labels

PART NO.	TYPE	Label Width (W) in. (mm)	Printable Area Height (H) in. (mm)	Label Height (H2) in. (mm)	Vertical Repeat in. (mm)	Horizontal Repeat in. (mm)	Liner Width in. (mm)	Labels per Row	Color	Qty. per Roll
TAG3T3-100B*	TAG3T3	1.00 (25.4)	1.00 (25.4)	3.75 (95.3)	4.00 (101.6)	1.00 (25.4)	3.35 (85.1)	3	White	3000
TAG38T4-100B*	TAG38T4	1.00 (25.4)	1.50 (38.1)	7.35 (186.7)	7.75 (196.8)	1.00 (25.4)	4.10 (104.1)	4	White	1000
TAG53T2-100B*	TAG53T2	1.50 (38.1)	0.70 (17.8)	1.43 (36.5)	1.62 (41.3)	1.50 (38.1)	3.35 (89.1)	2	White	2500
TAG1T1-100B*	TAG1T1	1.90 (48.3)	0.75 (19.1)	3.12 (79.2)	3.42 (86.8)	2.00 (50.8)	3.88 (98.4)	1	White	2500
TAG24T1-100B*	TAG24T1	2.00 (50.8)	0.50 (12.7)	1.43 (36.3)	1.68 (42.6)	2.00 (50.8)	2.20 (55.9)	1	White	1000
TAG10T2-100B*	TAG10T2	2.00 (50.8)	0.75 (19.1)	2.25 (57.2)	2.50 (63.5)	2.00 (50.8)	3.88 (98.4)	2	White	2500
TAG6T1-100B*	TAG6T1	2.00 (50.8)	1.50 (38.1)	3.75 (95.3)	4.00 (101.6)	2.00 (50.8)	2.20 (55.9)	1	White	1000
TAG7T1-100B*	TAG7T1	2.00 (50.8)	1.50 (38.1)	7.34 (186.4)	7.75 (196.8)	2.00 (50.8)	4.10 (104.1)	2	White	1000

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

*This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.