
















# Identification

## Labels

### Solar Identification

#### Preprinted Solar Labels - 443/552 Vinyl

PART NO.	TYPE	NEC Code	Label Width (W) in. (mm)	Label Height (H) in. (mm)	Color	Qty. per Pkg.	Drawing
596-00846*	IOCOD14	2014	2.00 (50.8)	1.25 (31.8)	Orange	50	
596-00880*	IOCOD17	2017	4.13 (104.4)	0.75 (19.1)	Orange	50	
596-00883*	IOCOD17ST	2017	2.00 (50.8)	1.25 (31.8)	Orange	50	
596-00826*	IOCODS	2014 (Spanish)	4.13 (104.6)	0.75 (19.1)	Orange	50	
596-00258*	WDCCU	2011	4.13 (104.6)	2.00 (50.8)	Red	50	
596-00588*		2014	4.13 (104.6)	2.00 (50.8)	Orange	50	
596-09323*	WDGC17	2017	3.75 (95.2)	2.00 (50.8)	Orange	50	
596-00231*	WDPSLBL	2011	4.13 (104.6)	0.75 (19.1)	Red	50	
596-00495*		2014, 2017	4.13 (104.6)	0.75 (19.1)	Orange	50	
596-00233*	WESHLBL	2011	3.75 (95.3)	2.00 (50.8)	Red	50	
596-00497*		2014	3.75 (95.3)	2.00 (50.8)	Orange	50	
596-00878*	WESHLBL17	2017	3.75 (95.2)	2.00 (50.8)	Orange	50	
596-00232*	WESHLBLDC	2011	3.75 (95.3)	2.50 (63.5)	Red	50	
596-00496*		2014	3.75 (95.3)	2.50 (63.5)	Orange	50	
596-00879*	WESHLBLDC17	2017	3.75 (95.2)	2.50 (63.5)	Orange	50	

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

\*This product meets UL standards. Please see appendix for specific file numbers. "Check-HT" is the mark of quality that represents a program of excellence in design and development over any other manufacturer in the industry.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.