

### Solar Identification

#### NEC Solar Label Convenience Packs - 443/552 Vinyl

PART NO.	TYPE	NEC Code	Label Width (W) in. (mm)	Label Height (H) in. (mm)	Color	Qty. per Pkg.	Drawing
596-00668*	IOCOD10	2014	4.12 (104.7)	0.75 (19.1)	Orange	10	
596-00884*	IOCOD17ST10	2017	2.00 (50.8)	1.25 (31.8)	Orange	10	
596-00895*	IOCOD1710	2017	4.13 (104.6)	0.75 (19.1)	Orange	10	
596-00670*	LAM110	Clear laminate, UV stable	4.20 (106.1)	2.25 (57.1)	Clear	10	
596-00743*	PSKWH10	2017	4.00 (101.6)	1.00 (25.4)	Red	10	
596-00747*	SMPV10	-	4.00 (101.6)	2.00 (50.8)	Orange	10	
596-00662*	WDCCU10	2014	4.12 (104.6)	2.00 (50.8)	Orange	10	
596-09324*	WDGC1710	2017	3.75 (95.3)	2.00 (50.8)	Orange	10	
596-00665*	WDPSLBL10	2014, 2017	4.12 (104.7)	0.75 (19.1)	Orange	10	
596-00660*	WESHLBL10	2014	3.75 (92.3)	2.00 (50.8)	Orange	10	
596-00893*	WESHLBL1710	2017	3.75 (92.3)	2.00 (50.8)	Orange	10	
596-00661*	WESHLBLDC10	2014	3.75 (92.3)	2.50 (63.5)	Orange	10	
596-00894*	WESHLBLDC1710	2017	3.75 (92.3)	2.50 (63.5)	Orange	10	
596-00663*	WGCME10	2014	4.12 (104.7)	2.00 (50.8)	Orange	10	
596-00664*	WTOPVLBL10	2014, 2017	4.12 (104.6)	2.00 (50.8)	Orange	10	

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

\*This product meets UL standards. Please see appendix for specific file numbers. "Check-HT" is the mark of quality that represents a program of excellence in design and development over any other manufacturer in the industry.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.