

Hook and Loop Grip Ties

Grip Tie Straps in 11" and 15" Lengths

PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width (W) in. (mm)	Width (W2) in. (mm)	Length (L2) in. (mm)	Material	Color	Pkg. Qty.
GT.75X150P2*	GT.75X15	50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Black	10
GT.75X150C2*		50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Black	100
GT.75X152P2*		50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Red	10
GT.75X152C2*		50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Red	100
GT.75X153P2*		50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Orange	10
GT.75X153C2*		50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Orange	100
GT.75X154P2*		50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Yellow	10
GT.75X154C2*		50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Yellow	100
GT.75X155P2*		50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Green	10
GT.75X155C2*		50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Green	100
GT.75X156P2*		50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Blue	10
GT.75X156C2*		50.0 (222.4)	15.0 (381.0)	3.9 (98.6)	0.8 (19.1)	1.5 (38.1)	2.5 (63.5)	PA66, PE	Blue	100

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.
 *This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.