

Hook and Loop Grip Ties

Write-On Grip Ties

In situations where instant identification is needed, HellermannTyton provides Grip Ties with a white write-on area. This smudge-free surface is ideal for fast and easy identification with a ballpoint pen or felt-tip marker. The write-on area is approximately 3/8"H x 1-1/4"W. It is positioned in the center of the black 6", 8", and 11" straps, as well as spaced every 12" on the Grip Tie rolls.

Features and Benefits

- Features quick release for repetitive access to cable and wire.
- Can be opened and closed numerous times without failure.
- Adjustable so one size can accommodate multiple bundle sizes.



PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width (W) in. (mm)	Width (W2) in. (mm)	Length (L2) in. (mm)	Material	Color	Pkg. Qty.
GT.50X60P2W	GT.50X6W	40.0 (177.9)	6.0 (152.4)	1.0 (25.4)	0.5 (12.7)	1.0 (25.4)	1.5 (38.1)	PA66, PE	Black	10
GT.50X60C2W		40.0 (177.9)	6.0 (152.4)	1.0 (25.4)	0.5 (12.7)	1.0 (25.4)	1.5 (38.1)	PA66, PE	Black	100
GT.50X80P2W	GT.50X8W	40.0 (177.9)	8.0 (203.2)	1.8 (44.5)	0.5 (12.7)	1.0 (25.4)	1.5 (38.1)	PA66, PE	Black	10
GT.50X80C2W		40.0 (177.9)	8.0 (203.2)	1.8 (44.5)	0.5 (12.7)	1.0 (25.4)	1.5 (38.1)	PA66, PE	Black	100
GT.50X110P2W	GT.50X11W	40.0 (177.9)	11.0 (279.4)	2.6 (66.8)	0.5 (12.7)	1.0 (25.4)	1.5 (38.1)	PA66, PE	Black	10
GT.50X110C2W		40.0 (177.9)	11.0 (279.4)	2.6 (66.8)	0.5 (12.7)	1.0 (25.4)	1.5 (38.1)	PA66, PE	Black	100

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.