

# Bundling and Securing

## Self-Affixing Cable Ties

### Arrowhead Mount Cable Ties

#### Push Mount Ties

PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Mounting Hole Dia. in. (mm)	Panel Thickness in. (mm)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width (W) in. (mm)	Material	Color	Pkg. Qty.
T50RSF9C2*	T50RSF(U)	50.0 (225.0)	0.25 - 0.28 (6.4 - 7.1)	0.04 - 0.14 (1.0 - 3.56)	8.3 (210.0)	1.7 (44.0)	0.2 (4.7)	PA66	Natural	100
T50RSF9M4*		50.0 (225.0)	0.25 - 0.28 (6.4 - 7.1)	0.04 - 0.14 (1.0 - 3.56)	8.3 (210.0)	1.7 (44.0)	0.2 (4.7)	PA66	Natural	1000
T50RSF0C2*		50.0 (225.0)	0.25 - 0.28 (6.4 - 7.1)	0.04 - 0.14 (1.0 - 3.56)	8.3 (210.0)	1.7 (44.0)	0.2 (4.7)	PA66HS	Black	100
T50RSF0M4*		50.0 (225.0)	0.25 - 0.28 (6.4 - 7.1)	0.04 - 0.14 (1.0 - 3.56)	8.3 (210.0)	1.7 (44.0)	0.2 (4.7)	PA66HS	Black	1000

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P. \*This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.