






### Arrowhead Mount Cable Ties

#### Wing Push Mount Ties

PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Mounting Hole Dia. in. (mm)	Panel Thickness in. (mm)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width (W) in. (mm)	Material	Color	Pkg. Qty.	Drawing
T50SL7. NN6P	T50SL7	50.0 (225.0)	0.27 - 0.28 (6.9 - 7.1)	0.03 - 0.10 (0.8 - 2.5)	6.5 (165.0)	1.3 (34.0)	0.2 (4.6)	PA66	Natural	500	
126-00082	T50SSF	50.0 (225.0)	0.24 - 0.26 (6.0 - 6.6)	0.03 - 0.12 (0.7 - 3.0)	6.3 (160.0)	1.4 (35.0)	0.2 (4.6)	PA66HIRHS	Natural	500	
126-00049		50.0 (225.0)	0.24 - 0.26 (6.0 - 6.6)	0.03 - 0.12 (0.7 - 3.0)	6.3 (160.0)	1.4 (35.0)	0.2 (4.6)	PA66HIRHS	Black	500	
126-00069		50.0 (225.0)	0.24 - 0.26 (6.0 - 6.6)	0.03 - 0.12 (0.7 - 3.0)	6.3 (160.0)	1.4 (35.0)	0.2 (4.6)	PA66	Natural	500	
126-02204	T50SSL5	50.0 (200.0)	0.24 - 0.26 (6.1 - 6.5)	0.02 - 0.11 (0.5 - 2.7)	5.3 (135.0)	1.0 (27.0)	0.2 (4.6)	PA66HS	Black	500	

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.  
 Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P. \*This product meets UL standards. Please see appendix for specific file numbers.