

## Specification Sheet

Part Number: MK7P



MK7 Pneumatic - Includes tool and quick connect fittings.

Article Number

110-07101

Type

MK7P

Color

Black (BK)

### Features & Benefits

- Enhanced technology for better application of cable ties.
- Improved compressed air supply for faster tensioning piston movement.
- Shorter processing time and greater volume of connecting tie application.
- Genuine potential for rationalization.
- Ergonomic design, molded handle to prevent slippage, reduce operator fatigue.
- Lightweight but very tough housing made of glass fiber-reinforced plastic.
- Meets high industry standards.
- Tensioning and cutting off cable ties flush with head by pressing one button.
- Smooth cut edge to prevent injuries.
- Automatic ejection of cut-off cable tie end.
- Three-level preset control to set tool tension.
- Optional safety cap to prevent tension setting from being changed by accident (important when bundling sensitive materials and maintaining process reliability.)
- Non-slip, comfortable grip, soft touch trigger, and one-touch tensioning/cut off.
- Very lightweight and easy to use on all cable ties 2.5–4.8 mm wide.
- All separately sold accessories are compatible with the MK7P series tool.

Quantity Per

carton

**Product Description**

The Mark 7 Pneumatic (MK7P) is built to perform in demanding production and manufacturing environments. Heavy duty precision parts ensure repeatability in the tensioning process. The MK7P fits comfortably in the operator's hand, reducing hand, arm and wrist fatigue. Due to its ergonomic features, HellermannTyton's MK7P makes it easier for the installer to consistently apply cable ties, while maintaining correct tension and flush cut-off. Safety is enhanced, as the MK7P can eliminate sharp edges of a cut-off cable tie.

**Short Description**

MK7 Pneumatic - Includes tool and quick connect fittings.

**Global Part Name**

MK7P-BK

**Technical Description**

Includes Mark 7 Pneumatic tool and quick connection fittings. Ergonomic tool uses pneumatic power and accomplishes rapid tension and cut-off with one trigger depression.

**Cable Ties**

T18 thru T50 Series CTT20 thru CTT60

**Cycle Time**

4 strokes per second

**Tension Setting Tools**

Adjustable

**Cable Tie Width Max (Imperial)**

0.18

**Power Supply**

Dry or lubricated air

**Tension Force**

60 to 170 N, adjustable

**ROHS Complaint**

Yes

**Package Quantity(Imperial)**

1

**Package Quantity (Metric)** 1

**Customs Number** 8467195090

**Weight (Metric)** 0.44

**Weight (Imperial)** 16